

Interface converter - PSM-EG-RS232/TTY-P/2K - 2761253

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Interface converter, for converting RS-232 to TTY, two channels, with electrical isolation, DIN-rail mountable

The figure shows a variant of the V.24 (RS-232)/RS-422 converter



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 064624
GTIN	4017918064624
Weight per Piece (excluding packing)	257.680 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---------------------------------------------------------------------------

Dimensions

Width	45 mm
Height	75 mm
Depth	110 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Degree of protection	IP20

General

Bit delay	≤ 3 μs
Bit distortion	≤ 5 %

Interface converter - PSM-EG-RS232/TTY-P/2K - 2761253

Technical data

General

Electrical isolation	VCC // V.24 (RS-232) // TTY
Test voltage data interfaces	2.5 kV AC
Test voltage data interface/power supply	2.5 kV AC
	2.5 kV
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 55022 / Class B
Net weight	257.68 g
Housing material	ABS
Color	green

Power supply

Nominal supply voltage	24 V DC \pm 20 %
Typical current consumption	130 mA (24 V DC)

Interfaces

Interface 1	V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1
Connection method	D-SUB 9 plug
	Pluggable screw connection
Transmission length	\leq 15 m (twisted pair)
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14
Serial transmission speed	\leq 19.2 kbps
Interface 2	TTY interface, CL2 in acc. with DIN 66348-1
Operating mode	Active, semi active, passive
Connection method	D-SUB-9 female connector
	Pluggable screw connection
Transmission length	\leq 1000 m (twisted pair)
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14
Load/output load current output	\leq 500 Ω
Serial transmission speed	\leq 19.2 kbps

Conformance/approvals

Designation	EAC
Identification	EAC

Interface converter - PSM-EG-RS232/TTY-P/2K - 2761253

Technical data

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 55022 / Class B

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	19179200
eCl@ss 7.0	19179290
eCl@ss 8.0	19179290
eCl@ss 9.0	19179290

ETIM

ETIM 2.0	EC000310
ETIM 3.0	EC000310
ETIM 4.0	EC000310
ETIM 5.0	EC000310
ETIM 6.0	EC000310
ETIM 7.0	EC000310

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43222604
UNSPSC 18.0	43222604
UNSPSC 19.0	43222604
UNSPSC 20.0	43222604
UNSPSC 21.0	43222604

Interface converter - PSM-EG-RS232/TTY-P/2K - 2761253

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	--	---------------

Accessories

Accessories

Adapter cable

Data cable - PSM-KA9SUB9/BB/2METER - 2799474



RS-232 cable, 9-pos. D-SUB socket on 9-pos. D-SUB socket, 9-wire, 1:1

Data plug

D-SUB bus connector - SUBCON 9/M-SH - 2761509



D-SUB connector, 9-pos., male connector, one cable entry < 35°, universal type for all systems, pin assignment: 1, 2, 3, 4, 5, 6, 7, 8, 9 to screw connection terminal block

Interface converter

Interface converter - PSM-ME-RS232/TTY-P - 2744458



Interface converter, for converting RS-232 (V.24) to TTY, with electrical isolation, 2 channels, rail-mountable

Interface converter - PSM-EG-RS232/TTY-P/2K - 2761253

Accessories

Mounting material

Shield connection clamp - ME-SAS - 2853899



Shield connection clamp for printed circuit terminal block

Screwdriver tools

Screwdriver - SZF 1-0,6X3,5 - 1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip
