

PRODUCT-DETAILS

# T6H 800 BREAKING PART 3p F F

# T6H 800 BREAKING PART 3p F F



## General Information

Extended Product Type	T6H 800 BREAKING PART 3p F F
Product ID	1SDA060337R1
EAN	8015644628055
Catalog Description	T6H 800 BREAKING PART 3p F F
Long Description	BREAKING PART TMAX T6H 800 FIXED THREE-POLE WITH FRONT TERMINALS

## Ordering

EAN	8015644628055
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

## Dimensions

Product Net Width	210 mm
Product Net Height	268 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	8.2 kg

## Container Information

Package Level 1 Units	1 piece
-----------------------	---------

Package Level 1 Width	305 mm
Package Level 1 Height	285 mm
Package Level 1 Depth / Length	370 mm
Package Level 1 Gross Weight	9.7 kg
Package Level 1 EAN	8015644628055

## Additional Information

Electrical Durability	5000 cycle 60 cycles per hour
Mechanical Durability	20000 cycle 120 cycles per hour
Number of Poles	3
Product Main Type	SACE Tmax T
Product Name	Moulded Case Circuit Breaker
Product Type	CBBU
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Rated Insulation Voltage ( $U_i$ )	1000 V
Rated Operational Voltage	690 V AC 750 V DC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(220 V AC) 100 kA (230 V AC) 100 kA (380 V AC) 70 kA (400 V AC) 70 kA (415 V AC) 70 kA (440 V AC) 50 kA (500 V AC) 50 kA (690 V AC) 19 kA
Rated Short-time Withstand Current ( $I_{cw}$ )	for 1 s 10 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(220 V AC) 100 kA (230 V AC) 100 kA (380 V AC) 70 kA (400 V AC) 70 kA (415 V AC) 70 kA (440 V AC) 50 kA (500 V AC) 50 kA (690 V AC) 25 kA (250 V DC) 2 Poles in Series 70 kA (500 V DC) 2 Poles in Series 50 kA (750 V DC) 3 Poles in Series 36 kA
Rated Uninterrupted Current ( $I_u$ )	800 A
Standards	IEC
Sub-type	T6
Suitable For	T6
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Fixed Circuit-Breakers Front
Test Voltage Max ( $U_{test}$ )	3500 V
Version	F

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210015D0201
Declaration of Conformity - CE	1SDL000165R0001

Environmental Information	1SDC210015D0201
Instructions and Manuals	1SDC210015D0201
RoHS Information	1SDL000200R0001

## Classifications

ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

## Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

