

PRODUCT-DETAILS

# T6N 1000 PR221DS-LS/I In=1000 3p F F

## T6N 1000 PR221DS-LS/I In=1000 3p F F



### General Information

Extended Product Type	T6N 1000 PR221DS-LS/I In=1000 3p F F
Product ID	1SDA060537R1
EAN	8015644630522
Catalog Description	T6N 1000 PR221DS-LS/I In=1000 3p F F
Long Description	C.BREAKER TMAX T6N 1000 FIXED THREE-POLE WITH FRONT TERMINALS AND SOLID-STATE RELEASE IN AC PR221DS-LS/I R 1000

### Ordering

EAN	8015644630522
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

### Dimensions

Product Net Width	210 mm
Product Net Height	268 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	12.863 kg

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	305 mm
Package Level 1 Height	285 mm
Package Level 1 Depth / Length	370 mm
Package Level 1 Gross Weight	11 kg
Package Level 1 EAN	8015644630522

## Additional Information

Electrical Durability	4000 cycle 60 cycles per hour
Mechanical Durability	20000 cycle 120 cycles per hour
Number of Poles	3
Power Loss	at Rated Operating Conditions per Pole 50 W
Product Main Type	SACE Tmax T
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current ( $I_n$ )	Main Circuit 1000 A
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Rated Insulation Voltage ( $U_i$ )	1000 V
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(220 V AC) 70 kA (230 V AC) 70 kA (380 V AC) 36 kA (400 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 30 kA (500 V AC) 25 kA (690 V AC) 15 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(220 V AC) 70 kA (230 V AC) 70 kA (380 V AC) 36 kA (400 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 30 kA (500 V AC) 25 kA (690 V AC) 20 kA (250 V DC) 2 Poles in Series 36 kA (500 V DC) 2 Poles in Series 25 kA (750 V DC) 3 Poles in Series 16 kA
Rated Uninterrupted Current ( $I_u$ )	1000 A
Release Type	EL
Standards	IEC
Sub-type	T6
Suitable For	T6
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Fixed Circuit-Breakers Front
Test Voltage Max ( $U_{test}$ )	3500 V
Version	F

## Certificates and Declarations (Document Number)

## Information

Declaration of Conformity - CE	1SDL000165R0006
Environmental Information	1SDL000143R0
GL Certificate	1SDL000163R0057
Instructions and Manuals	1SDH000511R0003

---

**Classifications**

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

**Categories**

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

