

PRODUCT-DETAILS

XT1B 160 TMD 125-1250 4p F F InN=100%

XT1B 160 TMD 125-1250 4p F F InN=100%



General Information

Extended Product Type	XT1B 160 TMD 125-1250 4p F F InN=100%
Product ID	1SDA066888R1
EAN	8015644007911
Catalog Description	XT1B 160 TMD 125-1250 4p F F InN=100%
Long Description	C.BREAKER TMAX XT1B 160 FIXED FOUR-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMD R 125-1250 A FULLY RATED NEUTRAL

Ordering

EAN	8015644007911
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	101.6 mm
Product Net Height	130 mm
Product Net Depth / Length	70 mm
Product Net Weight	1.378 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	128 mm
Package Level 1 Height	135 mm
Package Level 1 Depth / Length	143 mm
Package Level 1 Gross Weight	1.45 kg
Package Level 1 EAN	8015644007911

Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	Nr. Operations 240 cycles per hour Nr. Operations 25000 cycle
Number of Poles	4
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 10.7 W
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current (I_n)	125 A
Rated Frequency (f)	50 / 60 Hz
Rated Voltage (U_r)	690 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Instantaneous Short-Circuit Current Setting (I_i)	1250 A
Rated Insulation Voltage (U_i)	800 V
Rated Operational Voltage	690 V AC 500 V DC
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(220 V AC) 25 kA (230 V AC) 25 kA (240 V AC) 25 kA (380 V AC) 18 kA (415 V AC) 18 kA (440 V AC) 11.25 kA (500 V AC) 8 kA (525 V AC) 6 kA (690 V AC) 3 kA (250 V DC) 2 Poles in Series 18 kA (500 V DC) 3 Poles in Series 18 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(220 V AC) 25 kA (230 V AC) 25 kA (240 V AC) 25 kA (380 V AC) 18 kA (415 V AC) 18 kA (440 V AC) 15 kA (500 V AC) 8 kA (525 V AC) 6 kA (690 V AC) 3 kA (250 V DC) 2 Poles in Series 18 kA (500 V DC) 3 Poles in Series 18 kA
Rated Uninterrupted Current (I_u)	160 A
Release Type	TM
Setting Range	87,5...125 A

Standards	IEC
Sub-type	XT1
Terminal Connection Type	Fixed Circuit-Breakers Front
Version	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210100D0204 1SDC210099D0204
Declaration of Conformity - CE	9AKK106713A5532
Environmental Information	1SDL000190R0001
GL Certificate	1SDL000163R0103
Instructions and Manuals	1SDH000719R0001
LR Certificate	1SDL000163R0100

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

