



### Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2S
Product or component type	Switch-disconnector-fuse
Poles description	4P
Protected poles description	4t
Contacts type and composition	4 NO
[I <sub>th</sub> ] conventional free air thermal current	630 A (at 40 °C)
[I <sub>e</sub> ] rated operational current	400 A at 440 V 2 poles in series per phase and not juxtaposed DC-23A 630 A at 440 V 2 poles in series per phase and not juxtaposed DC-23B 315 A at 690 V AC-23A 400 A at 690 V AC-23B 500 A at 500 V AC-23A 500 A at 500 V AC-23B 630 A at 400 V AC-23A 630 A at 400 V AC-23B
Fuse type	BS
Fuse size	C1 C2
Network type	AC DC
Network frequency	50/60 Hz

### Complementary

Type of operating handle	Direct frontal External right side External frontal
Mounting support	Plate
[U <sub>i</sub> ] rated insulation voltage	1000 V AC 50/60 Hz
[U <sub>imp</sub> ] rated impulse withstand voltage	12 kV
Rated operational power in W	295 kW at 690 V 355 kW at 400 V 355 kW at 500 V 400 kW at 690 V
Making capacity	6300 A at 400 V AC-23B

[Icm] rated short-circuit making capacity	80 kA at 400 V with protection by gG fuses
Breaking capacity	5040 A at 400 V (AC-23B)
Short-circuit withstand	70 kA
Mechanical durability	8000 cycles
Electrical durability	1000 cycles AC-23A 1000 cycles AC-23B 200 cycles DC-23A 200 cycles DC-23B
Connections - terminals	Power circuit: bars63 mm <sup>2</sup> Power circuit: lugs-ring terminals 2 cable(s) 150 mm <sup>2</sup> Power circuit: lugs-ring terminals 2 cable(s) 300 mm <sup>2</sup>
Tightening torque	Power circuit: 44 N.m

## Environment

Standards	IEC 60947-3
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-40...80 °C
Fire resistance	850 °C fuse cover conforming to IEC 60695-2-1 960 °C body conforming to IEC 60695-2-1
Height	300 mm
Width	458 mm
Depth	250 mm
Net weight	20 kg

## Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------