

PRODUCT-DETAILS

SK-11

SK-11 Signal Contact



General Information

| | |
|-----------------------|------------------------------|
| Extended Product Type | SK-11 |
| Product ID | 1SAM101904R0003 |
| EAN | 4013614302213 |
| Catalog Description | SK-11 Signal Contact |
| Long Description | SK-11 Signal contact 1NO+1NC |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85369095 |

Popular Downloads

| | |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SBC100173C0201 |
| Instructions and Manuals | 2CDC131089M6801 |

Dimensions

| | |
|---------------------|-------|
| Product Net Width | 9 mm |
| Product Net Height | 86 mm |
| Product Net Depth / | 72 mm |

| | |
|--------------------|---------|
| Length | |
| Product Net Weight | 0.03 kg |

Technical

| | |
|---|---|
| Terminal Type | Screw Terminals |
| Rated Operational Voltage | 400 V AC 250 V DC Main Circuit 400 V AC |
| Rated Operational Current AC-15 (I_e) | (120 V) 3 A (240 V) 2 A (24 V) 3 A (380 / 400 V) 0.5 A |
| Rated Operational Current DC-13 (I_e) | (125 V) 0.55 A (24 V) 2.5 A (250 V) 0.23 A |
| Rated Frequency (f) | Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC |
| Rated Impulse Withstand Voltage (U_{imp}) | Auxiliary Circuit 6 kV |
| Rated Insulation Voltage (U_i) | 690 V |
| Degree of Protection | IP20 |
| Connecting Capacity Auxiliary Circuit | Flexible with Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 mm ² Flexible 1/2x 0.75 ... 1 mm ² Rigid 1/2x 1.0 ... 2.5 mm ² |
| Tightening Torque | Auxiliary Circuit 0.8 ... 1.0 N·m |
| Wire Stripping Length | Auxiliary Circuit 8 mm |
| Recommended Screw Driver | Pozidriv 2 |
| Number of Auxiliary Contacts NO | 0 |
| Number of Auxiliary Contacts NC | 1 |
| Standards | IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 |
| Product Name | Signal Contact |
| Suitable For | MS325 MO325 |
| Suitable for Product Class | Manual Motor Starter |
| Accessory Group | Electrical |
| Accessory Type | Signal Contact |

Technical UL/CSA

| | |
|--|---|
| Connecting Capacity Auxiliary Circuit UL/CSA | Flexible 1/2x 14-8 AWG Stranded 1/2x 14-18 AWG |
| Tightening Torque UL/CSA | Auxiliary Circuit 7 in·lb |
| Contact Rating UL/CSA | B300 Q300 |

Environmental

| | |
|-------------|--------------------------|
| Ambient Air | Operation -25 ... +50 °C |
|-------------|--------------------------|

| | |
|-------------|-----------------------------------|
| Temperature | Storage -50 ... +80 °C |
| RoHS Status | Following EU Directive 2011/65/EU |

Certificates and Declarations (Document Number)

| | |
|-----------------------------------|---|
| CCC Certificate | 1SAA918001-3801 |
| cUL Certificate | 1SAA918002-1701 |
| Declaration of Conformity - CE | 1SAD938517-0003 1SAD938510-0037 1SAD938513-0003 |
| GOST Certificate | 1SAA918000-2703 |
| Instructions and Manuals | 2CDC131089M6801 |
| RoHS Information | 1SAD938507-0037 1SAD938514-0003 |
| UL Certificate | 1SAA918002-1601 |

Container Information

| | |
|-----------------------------------|---------------|
| Package Level 1 Width | 210 mm |
| Package Level 1 Depth / Length | 79 mm |
| Package Level 1 Height | 105 mm |
| Package Level 1 Gross Weight | 0.365 kg |
| Package Level 1 EAN | 4013614442360 |
| Package Level 1 Units | 10 piece |

Classifications

| | |
|---------------------------------------|--|
| Object Classification Code | Q |
| ETIM 4 | EC002498 - Accessories for low-voltage switch technology |
| ETIM 5 | EC000041 - Auxiliary contact block |
| ETIM 6 | EC000041 - Auxiliary contact block |
| ETIM 7 | EC000041 - Auxiliary contact block |
| eClass | 7.0 27371302 |
| UNSPSC | 39121522 |
| IDEA Granular Category Code (IGCC) | 4742 >> Electrical contacts |

Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories

