



PRODUCT-DETAILS

## EPB25-316 CD-UK

### EPB25-316CD-UK-(width470mm)

#### General Information

Extended Product Type	EPB25-316 CD-UK
Product ID	1SKP816142C9751
EAN	6221115052072
Catalog Description	EPB25-316CD-UK-(width470mm)
Long Description	3 -phase protecta busbar type 16 way, surface, 250A, including Isolator kit EPB KIT 8C, with overall depth 160mm, and width 470 mm. (UK)

#### Ordering

EAN	6221115052072
Minimum Order Quantity	1 piece
Customs Tariff Number	85389769

#### Dimensions

Product Net Width	470 mm
Product Net Height	830 mm
Product Net Depth / Length	160 mm

#### Additional Information

Color	Grey
Cover Plate Type	Door
Degree of Protection	IP41
Housing Material	Steel
Mounting Type	Surface mounted (plaster)
Product Name	Sub Distribution
Protection Class	Grounded
Rated Current (I <sub>n</sub> )	250 A
Surface Finishing	Powder coating

#### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SKC802015C0203
Declaration of	1SKC100819C0001

Conformity - CE

Instructions and  
Manuals

1SKC802015C0203

---

## Classifications

ETIM 6

EC000058 - Empty cabinet

ETIM 7

EC000058 - Empty cabinet

WEEE Category

Product Not in WEEE Scope

---

## Categories

Low Voltage Products and Systems → Enclosures → Sub Distribution Boards → Sub Distribution Boards