

PRODUCT-DETAILS

# DSE201 C20 A30 - N Blue

## DSE201 C20 A30 - N Blue - RCBO



### General Information

Extended Product Type	DSE201 C20 A30 - N Blue
Product ID	2CSR255151R1204
EAN	8012542659129
Catalog Description	DSE201 C20 A30 - N Blue - RCBO
Long Description	DSE201 is a 1P+N residual current circuit breaker with overcurrent protection (RCBO) in one module for the protection against short-circuit currents, overload, earth fault currents, indirect contacts, additional protection against direct contacts (30 mA versions). DSE201 is equipped with supply neutral wire and functional earth wire.

### Technical

Standards	IEC 61009-1 IEC 61009-2-2 AS/NZS 61009-1
Type of Residual Current	A type
Number of Poles	1+N
Number of Protected Poles	1
Rated Current ( $I_n$ )	20 A
Rated Voltage ( $U_r$ )	230-240 V AC
Rated Insulation Voltage ( $U_i$ )	500 V

Overvoltage Category	III
Pollution Degree	2
Test Voltage (Ut)	195 ... 264 V
Rated Frequency (f)	50...60 Hz
Rated Short-Circuit Capacity (I <sub>cn</sub> )	(230 / 400 V AC) 6 kA
Rated Residual Breaking Capacity (I <sub>Δm</sub> )	6 kA
Primary Rated Impulse Withstand Voltage	4 kV
Dielectric Test Voltage	2.5 kV
Tripping Characteristic	C
Energy Limiting Class	3
Housing Type	Insulation group II, RAL 7035
Actuator Type	Toggle - Insulation group IIIA, black, sealable in ON-OFF positions
Electrical Endurance	10000 cycle 20000 cycle
Degree of Protection	Housing IP40 Terminals IP20
Resistance to Shock acc. to IEC 60068-2-27	30g / 2 shocks / 13 ms
Resistance to Vibrations acc. to IEC 60068-2-6	0.35mm or 5g - 20 cycles at 5...150...5 Hz without load
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Reference Ambient Air Temperature	30 °C
Terminal Type	Screw Terminals
Screw Terminal Type	Cage Terminal
Connecting Capacity	Busbar 10 mm <sup>2</sup> Rigid 25 ...25 mm <sup>2</sup> Flexible 25 ...25 mm <sup>2</sup>
Tightening Torque	Top 1.2 N·m Bottom 2.8 N·m
Mounting Type	on DIN rail EN 60715 (35 mm) by means of fast clip device in consumer unit Type A according to IEC 61439-1&3, BS EN 61439-1&3, in distribution board Type B according to IEC 61439-1&3, BS EN 61439-1&3.
Power Supply Connection	Bottom
Position of Neutral Terminals	Right
Power Loss	5.5 W

## Environmental

Ambient Air Temperature	Operation -25...55 °C
RoHS Status	Following EU Directive 2011/65/EU

## Dimensions

Product Net Width	0.018 m
Product Net Height	0.100 m

Product Net Depth / Length	0.069 m
Product Net Weight	0.180 kg

---

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.036 m
Package Level 1 Height	0.088 m
Package Level 1 Depth / Length	0.143 m
Package Level 1 Gross Weight	0.200 kg
Package Level 1 EAN	8012542659129

---

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5595
Environmental Information	refer to RoHS information
Instructions and Manuals	9AKK106930A0912
RoHS Information	2CSC422006K2701

---

## Popular Downloads

Data Sheet, Technical Information	9AKK106930A0940
Instructions and Manuals	9AKK106930A0912

---

## Classifications

Object Classification Code	Q
ETIM 4	EC000905 - Earth leakage circuit breaker
ETIM 5	EC000905 - Earth leakage circuit breaker
ETIM 6	EC000905 - Earth leakage circuit breaker
ETIM 7	EC000905 - Earth leakage circuit breaker

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

