



## Main

|  |   |
|--|---|
| Range                                  | TeSys   |
| Product name                           | TeSys D   |
| Product or component type              | Star delta starter  |
| Device short name                      | LC3D  |
| Contacteur application                 | Motor control   |
| Utilisation category                   | AC-3  |
| Device presentation                    | Pre-wired   |
| Poles description                      | 3 x 3P  |
| Power pole contact composition         | 3 x 3 NO  |
| [Ue] rated operational voltage         | Power circuit: $\leq 690$ V AC 25...400 Hz  |
| [Ie] rated operational current         | 80 A (at $\leq 60$ °C) at $\leq 440$ V AC AC-3 for power circuit  |
| Motor power kW                         | 37 kW at 220/230 V AC 50/60 Hz<br>75 kW at 380/400 V AC 50/60 Hz<br>75 kW at 415 V AC 50/60 Hz<br>75 kW at 440 V AC 50/60 Hz  |
| Control circuit type                   | AC at 50/60 Hz  |
| [Uc] control circuit voltage           | 24 V AC 50/60 Hz  |
| Auxiliary contact composition          | 1 NC for KM2 line contactor<br>1 NO for KM3 delta contactor   |
| [Uimp] rated impulse withstand voltage | 8 kV conforming to IEC 60947  |
| Overvoltage category                   | III   |
| [Ui] rated insulation voltage          | Power circuit: 600 V CSA certified<br>Power circuit: 600 V UL certified<br>Signalling circuit: 600 V CSA certified<br>Signalling circuit: 600 V UL certified<br>Power circuit: 1000 V conforming to IEC 60947-4-1<br>Signalling circuit: 1000 V conforming to IEC 60947-1 |
| Electrical durability                  | 10 Mcycles 80 A AC-3 at $U_e \leq 440$ V  |
| Interlocking type                      | Mechanical  |
| Mounting support                       | Plate   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                        |   |
|------------------------|---|
| Standards              | CSA C22.2 No 14<br>UL 508<br>EN 60947-5-1<br>IEC 60947-4-1<br>EN 60947-4-1<br>IEC 60947-5-1 |
| Product certifications | DNV<br>UL<br>CSA<br>LROS (Lloyds register of shipping)<br>GL<br>RINA<br>GOST<br>BV<br>CCC   |

## Complementary

|                                 |  |
|---------------------------------|--|
| Connections - terminals         | Control circuit: screw clamp terminals 1 1...4 mm <sup>2</sup> - cable stiffness: flexible without cable end<br>Control circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - cable stiffness: flexible without cable end<br>Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end<br>Control circuit: screw clamp terminals 1 1...4 mm <sup>2</sup> - cable stiffness: solid without cable end<br>Control circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - cable stiffness: solid without cable end<br>Power circuit: screw clamp terminals 1 4...50 mm <sup>2</sup> - cable stiffness: flexible without cable end<br>Power circuit: screw clamp terminals 2 4...25 mm <sup>2</sup> - cable stiffness: flexible without cable end<br>Power circuit: screw clamp terminals 1 4...50 mm <sup>2</sup> - cable stiffness: flexible with cable end<br>Power circuit: screw clamp terminals 2 4...16 mm <sup>2</sup> - cable stiffness: flexible with cable end<br>Power circuit: screw clamp terminals 1 4...50 mm <sup>2</sup> - cable stiffness: solid without cable end<br>Power circuit: screw clamp terminals 2 4...25 mm <sup>2</sup> - cable stiffness: solid without cable end<br>Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end |
| Tightening torque               | Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>Power circuit: 9 N.m - on screw clamp terminals - with screwdriver flat Ø 6...8 mm  |
| Mechanical durability           | 4 Mcycles  |
| Maximum operating rate          | 30 cyc/h 60 °C   |
| Starting time                   | 30 s   |
| Coil technology                 | Without built-in suppressor module   |
| Control circuit voltage limits  | Drop-out: 0.3...0.6 U <sub>c</sub> at 50/60 Hz (at <55 °C)<br>Operational: 0.8...1.1 U <sub>c</sub> at 50 Hz (at <55 °C)<br>Operational: 0.85...1.1 U <sub>c</sub> at 60 Hz (at <55 °C)  |
| Inrush power in VA              | 140 VA 60 Hz cos phi 0.75 (at 20 °C)<br>160 VA 50 Hz cos phi 0.75 (at 20 °C)   |
| Hold-in power consumption in VA | 13 VA 60 Hz cos phi 0.3 (at 20 °C)<br>15 VA 50 Hz cos phi 0.3 (at 20 °C)   |
| Heat dissipation                | 4...5 W at 50/60 Hz  |
| Auxiliary contacts type         | Mechanically linked conforming to IEC 60947-5-1 3 x 1 NO + 1 NC<br>Mirror contact conforming to IEC 60947-4-1 3 x 1 NC   |
| Signalling circuit frequency    | 25...400 Hz  |
| Minimum switching current       | 5 mA for signalling circuit  |
| Minimum switching voltage       | 17 V for signalling circuit  |
| Non-overlap time                | 1.5 ms on de-energisation between NC and NO contact<br>1.5 ms on energisation between NC and NO contact  |
| Width                           | 311 mm   |
| Height                          | 143 mm   |
| Depth                           | 183 mm   |
| Net weight                      | 5.4 kg   |

## Environment

|                                     |   |
|-------------------------------------|---|
| Insulation resistance               | > 10 MOhm for signalling circuit        |
| IP degree of protection             | IP20 front face conforming to IEC 60529 |
| Protective treatment                | TH conforming to IEC 60068-2-30         |
| Pollution degree                    | 3                                       |
| Ambient air temperature for storage | -60...80 °C                             |

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -40...70 °C at Uc   |
| Operating altitude                    | 3000 m without  |
| Fire resistance                       | 850 °C conforming to IEC 60695-2-1  |
| Flame retardance                      | V1 conforming to UL 94  |
| Mechanical robustness                 | Vibrations contactor open: 2 Gn, 5...300 Hz<br>Shocks contactor open: 8 Gn for 11 ms<br>Vibrations contactor closed: 3 Gn, 5...300 Hz<br>Shocks contactor closed: 10 Gn for 11 ms |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End of Life Information</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|