

ENYCAP™ Energy storage Capacitor 220 EDLC 100F – 2,7V – 20x40mm

FEATURES


- Polarized Electrical Double Layer Capacitor
- Very high energy and power density
- Rapid charge and discharge
- High number of cycles > 500.000 times
- Wide temperature range
- RoHS compliant

MECHANICAL / PHYSICAL DATA

ϕD_{Max}	20,5 mm
L_{Max}	43,5 mm
ϕd	1,0 mm
F	7,5 ± 0,5 mm
Weight	20,0 g

PACKAGING

Form CA, 100 pieces per box (=smallest packing quantity)



QUICK REFERENCE: ELECTRICAL DATA (at 20°C, unless otherwise specified)

Capacitance, initial C_R	100 F
Tolerance on C_R , initial	-20% / +50 %
Rated voltage, U_R (T_{MAX} 65°C / 85°C)	2,7 V / 2,3 V
Surge voltage, U_S (< 1sec, non repetitive)	2,85 V
Max. ESR_{DC} , initial ⁽²⁾	15 m Ω
Max. peak current, I_{Peak} ⁽³⁾ (65°C / 85°C)	35 A / 30 A
Max. leakage Current after 0,5 h / 72 hours, I_{L1}	50 mA / 500 μ A
Stored energy E at U_R (65°C / 85°C)	0,1Wh / 0,07 Wh
Specific energy E_d at U_R (65°C / 85°C)	5,0 Wh/kg / 3,7 Wh/kg
Operating temperature range:	
Minimum, T_{MIN}	-40 °C
Maximum, T_{MAX} (U_R 2,7V / 2,3V)	+65°C / +85°C
Useful life:	1.000 hours @ U_R , T_{MAX}

Further characteristics for series **220 EDLC** are specified in our data sheet at www.vishay.com.

Data sheet series **220 EDLC**: <http://www.vishay.com/capacitors/list/product-28421/>

This data sheet is subject to change without notice. THE INFORMATION PROVIDED HEREIN IS SUBJECT TO SPECIFIC DISCLAIMERS AS SET FORTH AT <http://www.vishay.com/docs/91000/disclaimer.pdf>



Preliminary

ENYCAP™ Energy storage Capacitor 220 EDLC 100F – 2,7V – 20x40mm

CONDITIONS (electrical measurements at 20°C, unless otherwise specified)⁽¹⁾:

Capacitance C_R and ESR_{DC}	Measured by DC discharging method as described in "Measuring of Characteristics". (2)
Maximum peak current	Non repetitive current for maximum 1 s at specified operating temperature. Maximum operating voltage (refer to derating table) must not be exceeded. Usually to be tested with constant current discharge from U to $0,5 \cdot U_R$. Max. Current should not be used in normal operation and is only provided as reference value.
Leakage current I_L	Measured at U_R . Capacitor is charged to the rated voltage at 20 °C. Leakage current is the current at specified time that is required to keep the capacitor charged at the rated voltage.
Useful life	After loading the capacitor for the specified time at maximum specified temperature $T_{max.} = 85 \text{ °C}$ and related maximum operating voltage $U = 2,3 \text{ V}$, following parameters are valid within a timeframe of 1000 h:
Capacitance	Within $\pm 50\%$ of minimum initial specified value.
ESR	Less than 4 x initial specified value.
Leakage	Within specified value.
Storage at upper category temperature	After loading the capacitor for the specified time at maximum specified temperature $T_{max.} = 85 \text{ °C}$ and without charge and under 40 % RH, following parameters are valid within a timeframe of 1000 h:
Capacitance	Within $\pm 30 \%$ of minimum initial specified value.
ESR	Less than 3 x initial specified value.
Leakage	Within specified value.
Cycle life	Cycles at 20 °C between rated voltage and half of rated voltage U_R with constant current and 1 s rest between charge and discharge: > 500 000 cycles
Capacitance	Within $\pm 30\%$ of minimum initial specified value.
ESR	Less than 2 x initial specified value.
Stored energy E, specific energy E_d and E_v	$E \text{ [Wh]} = \frac{1}{2} \times C \times (U_R)^2 \times 1/3600$ $E_d \text{ [Wh/kg]} = \frac{1}{2} \times C \times (U_R)^2 \times 1/3600 \times 1/\text{mass}$ $E_v \text{ [Wh/L]} = \frac{1}{2} \times C \times (U_R)^2 \times 1/3600 \times 1/\text{volume}$
Soldering	Hand or wave soldering allowed. For details refer to soldering requirements for radial aluminum electrolytic capacitors in supplementary document.
Cleaning	For printed circuit board cleaning, apply only non aggressive cleaning agents. For details refer to cleaning requirements for Aluminum electrolytic capacitors in supplementary document.
Environmental conditions	Do not expose capacitors to <ul style="list-style-type: none"> • temperatures outside specified range. • high humidity atmospheres. • corrosive atmospheres, e.g. halogenides, sulphurous or nitrous gases, acid or alkaline solutions, etc. • environments containing oil and grease.

Notes

- General remark: temperatures to be measured at capacitor case
- (1) Conditions: electrical measurements at 20 °C, unless otherwise specified
- (2) Rated capacitance C_R and ESR_{DC} ; measurement current acc. IEC 62391-1
- (3) See table above, pos. maximum peak current

Further characteristics for series **220 EDLC** are specified in our data sheet at www.vishay.com.

Data sheet series **220 EDLC**: <http://www.vishay.com/capacitors/list/product-28421/>

This data sheet is subject to change without notice. THE INFORMATION PROVIDED HEREIN IS SUBJECT TO SPECIFIC DISCLAIMERS AS SET FORTH AT <http://www.vishay.com/docs/91000/disclaimer.pdf>



Preliminary

ENYCAP™ Energy storage Capacitor 220 EDLC
100F – 2,7V – 20x40mm

REVISION HISTORY

Rev #	Date	Name	Change
0	Nov 13 th , 2019	GT	Initial version
1	May 27 th , 2020	GT	Electrical data update

This data sheet is subject to change without notice. THE INFORMATION PROVIDED HEREIN IS SUBJECT TO SPECIFIC DISCLAIMERS AS SET FORTH AT <http://www.vishay.com/docs/91000/disclaimer.pdf>



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

This data sheet is subject to change without notice. THE INFORMATION PROVIDED HEREIN IS SUBJECT TO SPECIFIC DISCLAIMERS AS SET FORTH AT <http://www.vishay.com/docs/91000/disclaimer.pdf>