

# KRM55TR72E225MH01#


“#” indicates a package specification code.



< List of part numbers with package codes >

KRM55TR72E225MH01K      KRM55TR72E225MH01L

## Appearance & Shape



## References

Packaging	Specifications	Minimum Order Quantity
K	330Embossed Tape	1000
L	180Embossed Tape	400

Mass (typ.)	
1 piece	0.62g

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# KRM55TR72E225MH01#

“#” indicates a package specification code.

## Specifications

Length	6.1±0.4mm
Width	5.3±0.2mm
Thickness	4.8±0.2mm
Capacitance	2.2μF ±20%
Metal terminal width e	1.2±0.2mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	250Vdc
Capacitance change rate	±15%
Temperature characteristics (complied standard)	X7R(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# KRM55TR72E225MH01#

“#” indicates a package specification code.




## Characteristic Data


The charts below may show another part number which shares its characteristics.




■ KRM55TR72E225MH01 |Z| DCOV, 25degC



■ KRM55TR72E225MH01 R DCOV, 25degC



■ KRM55TR72E225MH01 C-DC bias capchange, 25.0degC, AC1V



■ KRM55TR72E225MH01 C-AC Voltage capchange, DCOV, 25.0d

**Attention**


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# KRM55TR72E225MH01#

“#” indicates a package specification code.



■ KRM55TR72E225MH01 C-Temp. capchange, DCOV, AC1Vrms



KRM55TR72E225MH01 Temp. rise ■ 50kHz ■ 100kHz ■ 300kHz

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.