

TECHNICAL DATA SHEET

PRO-POWER

RoHS
Compliant

CW1308F 6 PAIR TELEPHONE CABLE CB19780

Design of cable	
Inner conductor:	1/0.40±0.005mm Strand Bare Copper
Insulation:	PVC
Size:	Ø0.7±0.1mm
Colour	Blue/White Orange/White Green/White Brown/White Grey/White Red/Blue Wire with ring
6 pairs stranded to a qual:	
PET Overlapped:	
Rip wire:	
Jacket:	PVC
Colour:	White
Size of jacket:	Ø5.2±0.2mm
Wall thickness:	≈0.7mm
Printing:	By request
Electric data at 20°C	
Conductor resistance:	≤145.0Ω/km
Insulation resistance:	≥200 MΩ*km
Testing voltage:	wire/wire/screen 50Hz 1min=800V
Miscellaneous	
Permissible temperature:	-10°C~60°C
Packaging:	100M on non-returnable reel

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

PRO-POWER