

## TEROSON MS 934

April 2014

### PRODUCT DESCRIPTION

TEROSON MS 934 provides the following product characteristics:

<b>Technology</b>	Silane-modified polymer
<b>Product Type</b>	Sealant
<b>Components</b>	One-component
<b>Cure</b>	Humidity
<b>Application</b>	Assembly
<b>Appearance</b>	transparent
<b>Consistency</b>	Pasty, Thixotropic
<b>Odor</b>	Characteristic

TEROSON MS 934 is a gun-grade, one-component sealant based on silane modified polymers, which cures by reaction with moisture to an elastic product. The skin formation and curing times are dependent on humidity and temperature, and the curing time also depends on joint depth. By increasing the temperature and moisture these times can be reduced; low temperature as well as low moisture retard the process. . TEROSON MS 934 is free of solvents, isocyanates, silicones and PVC. . It demonstrates good adhesion to many substrates and is compatible with suitable paint systems. TEROSON MS 934 can be damaged under UV load.

### Application Areas:

TEROSON MS 934 is used for special applications and has to be painted over exterior applications.

### TECHNICAL DATA

Density, g/cm <sup>3</sup> :	approx. 1.05
<b>Miscellaneous:</b>	
Sag resistance:	no sagging (DIN profile 15 mm)
Skin formation time, min*:	approx. 5
Cure rate, mm/24 hrs:	approx. 3
Shore-A-hardness (DIN 53505):	approx. 35
Tensile strength (acc. to DIN 53504), MPa:	approx. 1.8
Elongation at break (acc. to DIN 53504),%:	approx. 250
Stress at 100 % elongation (acc. to DIN 53504), MPa:	approx. 0.9
Volume change (acc. to DIN 52451), %:	<2

Application temperature, °C:	5 to 40
In service temperature range, °C:	-40 to +80
Short exposure (up to 1 h), °C:	120

\* DIN 50014 standard climate: 23°C, 50% relative air humidity

### DIRECTIONS OF USE

#### Preliminary Statement:

Prior to use it is necessary to read the **Material Safety Data Sheet** for information about precautionary measures and safety recommendations. Also, for chemical products exempt from compulsory labeling, the relevant precautions should always be observed.

#### Adhesion:

Depending on the surface it can be necessary to roughen the surface or to use primer such as Teroson SB 450 as an adhesion promoter to provide optimum adhesion.

#### Pre-Treatment:

The substrates must be clean, dry, oil- and grease free. Depending on the surface it can be necessary to roughen the surface or to use a primer/adhesion promoter to provide best adhesion. . When bonding and sealing PMMA, e.g. Plexiglas® and polycarbonate, e.g. Makrolon® or Lexan®, under tension, stress corrosion cracking may occur. In such cases Teroson MS 934 should not be utilised. There is no adhesion to polyethylene, polypropylene and PTFE (e.g. Teflon®). Substrates not mentioned above should be subject to trials.

#### Application:

Application from 310 ml cartridges is made with the Teroson Hand or Air Pressure Pistols with a piston rod. In the case of compressed air application a pressure of 2 to 5 bar is required. Low material temperatures of the sealant will lead to an increase of viscosity, resulting in a lower extrusion rate. This can be avoided by bringing the sealant up to room temperature prior to application.

#### Cleaning:

For cleaning application equipment contaminated with uncured TEROSON MS 934 we recommend the use of cleaners Teroson A, D or FL+.

**Classification:**

Reference 0.0

Please refer to the corresponding **Material Safety Data Sheets** for details on:

**Hazards identification**  
**Transport information**  
**Regulatory information**

**Storage:****Shelf life:**

Frost-Sensitive	No
Recommended storage temperature, °C	10 to 25
Shelf-life (in unopened original packaging)	12 months

**Disclaimer****Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned

herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

**Henkel AG & Co. KGaA**  
 40191 Düsseldorf, Germany  
 Phone: +49-211-797-0

**Henkel Corporation**  
 Rocky Hill, CT 06067, USA  
 Phone: +1-860-571-5100

**Henkel (China) Co. Ltd.**  
 201203 Shanghai, China  
 +86.21.2891.8000

For more information, please contact us on [www.henkel.com](http://www.henkel.com)