

60/40 Alloy Rosin Flux

Solder Wire



Properties:

- Good wetting on most common surfaces.
- Two activity levels: Multicomp 362 for general work and Multicomp 366 for more difficult surfaces.
- Non-corrosive.
- Fast soldering.
- Rosin based.
- Halide activated.

Product Range:

Multicomp 362 and 366 cored wires are manufactured with a range of flux contents. Although users will normally be using products with a nominal flux content of 3%.

Multicomp 362 and 366 cored wires are available in a variety of alloys conforming to J-STD-006 and EN 29453 or alloys conforming to similar national or international standards. For details refer to document "Properties of Alloys used in Cored Solder Wires". A wide range of wire diameters is available.

Alternative flux contents and alloys may be manufactured to special order.

Technical Specification:

A full description of test methods and detailed test results are available on request.

Alloys:

The alloys used for Multicomp flux cored solder wires conform to the purity requirements of the common national and international standards. A wide range of wire diameters is available manufactured to close dimensional tolerances.

Flux:

Multicomp 362 and 366 solid flux leave dry and non-sticky residues. In use its odour is typically that of rosin fluxes.

Typical Flux Properties		
Test	362	366
Acid value	170mgKOH/g	158mgKOH/g
Halide content	<0.5%	1.0%
SIR Test (without cleaning) J-STD-004	Pass	Pass
Classification J-STD-004 EN29451-1	ROL1 1.1.2	ROM1 1.1.2

Special Properties:

Surface Insulation Resistance:

Surface Insulation Resistance: Multicomp 362 and 366 flux pass the J-STD-004 SIR test and other elements of J-STD-004 test protocols associated with the flux classification ROL1 for 362 and ROM1 for 366.

Electromigration Test: Multicomp 362 and 366 pass the Bellcore GR-78-CORE Electromigration test.

Recommended Operating Conditions:

Soldering Iron:

Good results should be obtained using a range of tip temperatures. However, the optimum tip temperature and heat capacity required for a hand soldering process is a function of both soldering iron design and the nature of the task and care should be exercised to avoid unnecessarily high tip temperatures for excessive times. A high tip temperature will increase any tendency to flux spitting and it may produce some residue darkening.



60/40 Alloy Rosin Flux

Solder Wire



The soldering iron tip should be properly tinned and this may be achieved using Multicomp cored wire. Severely contaminated soldering iron tips should first be cleaned and pre-tinned using Multicomp Tip Tinner/Cleaner TTC1, then wiped on a clean, damp sponge before re-tinning with Multicomp cored wire.

Soldering Process:

Multicomp cored wires contain a careful balance of resins and activators to provide clear residues, maximum activity and high residue reliability, without cleaning in most situations. To achieve the best results from Multicomp solder wires, recommended working practices for hand soldering should be observed as follows:

- Apply the soldering iron tip to the work surface, ensuring that it simultaneously contacts the base material and the component termination to heat both surfaces adequately. This process should only take a fraction of a second.
- Apply Multicomp flux cored solder wire to a part of the joint surface away from the soldering iron and allow to flow sufficiently to form a sound joint fillet-this should be virtually instantaneous. Do not apply excessive solder or heat to the joint as this may result in dull, gritty fillets and excessive or darkened flux residues.
- Remove solder wire from the work piece and then remove the iron tip.

The total process will be very rapid, depending upon thermal mass, tip temperature and configuration and the solderability of the surfaces to be joined.

Multicomp flux cored solder wires provide fast soldering on copper and brass surfaces as well as solder coated materials. Activity of the halide activated versions on nickel is also good depending on the state of oxidation of the nickel finish. The good thermal stability of Multicomp fluxes means they are also well suited to soldering applications requiring high melting temperature alloys.

Cleaning:

Multicomp 362 and 366 cored solder wires have been formulated to leave pale flux residues and to resist spilling and fuming. Cleaning will not be required in most situations but if necessary this is best achieved using Multicomp MCF800 Cleaner. Other proprietary solvent or semi-aqueous processes may be suitable. Saponification may be viable but customers must ensure that the desired level of cleanliness can be achieved by their chosen system.

Health and Safety:

Warning:

The following information is for guidance only.

Health Hazards and Precautions: Inhalation of the flux fumes given off during soldering should be avoided. The fumes are irritating to the throat and respiratory system. Prolonged or repeated exposure to rosin or modified rosin based flux fumes may lead to the development of respiratory sensitisation and occupational asthma.

Multicomp solder wires must always be used with suitable fume extraction equipment to remove fumes from the breathing zone of operators and the general work environment.

Solder alloys containing lead give off negligible fume at normal soldering temperatures up to 500°C.

Normal handling of lead alloy wires will not cause lead to be absorbed through the skin. The most likely route of entry is through ingestion but this will not be significant if a good standard of personal hygiene is maintained. Eating, drinking and smoking should not be permitted in the working area. Hands should be washed with soap and warm water after handling solder wire.

Waste disposal:

Wherever possible, waste solder wire should be recycled for recovery of metal. Otherwise it should be disposed of according to local or national regulations.

60/40 Alloy Rosin Flux

Solder Wire



Part Number Table

Description	Part Number
Solder, 60/40 Rosin 0.5mm 250g	507-1057
Solder, 60/40 Rosin 0.7mm 250g	507-1069
Solder, 60/40 Rosin 0.9mm 250g	507-1070
Solder, 60/40 Rosin 1.2mm 250g	507-1082
Solder, 60/40 Rosin 0.7mm 500g	507-1100
Solder, 60/40 Rosin 0.9mm 500g	507-1112
Solder, 60/40 Rosin 1.2mm 500g	507-1124

60/40 Alloy Rosin Flux

Solder Wire



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

