



## Main

|  |  |
|--|--|
| Range                                  | TeSys  |
| Product name                           | TeSys D  |
| Product or component type              | Contacteur   |
| Device short name                      | LC1D   |
| Contacteur application                 | Motor control<br>Resistive load  |
| Utilisation category                   | AC-3<br>AC-4<br>AC-1   |
| Poles description                      | 3P   |
| Power pole contact composition         | 3 NO   |
| [Ue] rated operational voltage         | Power circuit: $\leq 690$ V AC 25...400 Hz<br>Power circuit: $\leq 300$ V DC   |
| [Ie] rated operational current         | 50 A (at $\leq 60$ °C) at $\leq 440$ V AC AC-1 for power circuit<br>38 A (at $\leq 60$ °C) at $\leq 440$ V AC AC-3 for power circuit   |
| Motor power kW                         | 18.5 kW at 500 V AC 50/60 Hz (AC-3)<br>18.5 kW at 660...690 V AC 50/60 Hz (AC-3)<br>7.5 kW at 400 V AC 50/60 Hz (AC-4)<br>18.5 kW at 380...400 V AC 50/60 Hz (AC-3)<br>9 kW at 220...230 V AC 50/60 Hz (AC-3)<br>18.5 kW at 415...440 V AC 50/60 Hz (AC-3)   |
| Motor power HP (UL / CSA)              | 10 hp at 230/240 V AC 50/60 Hz for 3 phases motors<br>10 hp at 200/208 V AC 50/60 Hz for 3 phases motors<br>5 hp at 240 V AC 50/60 Hz for 1 phase motors<br>20 hp at 480 V AC 50/60 Hz for 3 phases motors<br>25 hp at 600 V AC 50/60 Hz for 3 phases motors |
| Control circuit type                   | AC at 50/60 Hz   |
| [Uc] control circuit voltage           | 42 V AC 50/60 Hz   |
| Auxiliary contact composition          | 1 NO + 1 NC  |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947   |
| Overvoltage category                   | III  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|  |   |
|--|---|
| [I <sub>th</sub> ] conventional free air thermal current | 10 A (at 60 °C) for signalling circuit<br>50 A (at 60 °C) for power circuit   |
| I <sub>rms</sub> rated making capacity                   | 140 A AC for signalling circuit conforming to IEC 60947-5-1<br>250 A DC for signalling circuit conforming to IEC 60947-5-1<br>550 A at 440 V for power circuit conforming to IEC 60947  |
| Rated breaking capacity                                  | 550 A at 440 V for power circuit conforming to IEC 60947  |
| [I <sub>cw</sub> ] rated short-time withstand current    | 60 A 40 °C - 10 min for power circuit<br>430 A 40 °C - 1 s for power circuit<br>150 A 40 °C - 1 min for power circuit<br>310 A 40 °C - 10 s for power circuit<br>100 A - 1 s for signalling circuit<br>120 A - 500 ms for signalling circuit<br>140 A - 100 ms for signalling circuit   |
| Associated fuse rating                                   | 10 A gG for signalling circuit conforming to IEC 60947-5-1<br>63 A gG at ≤ 690 V coordination type 1 for power circuit<br>63 A gG at ≤ 690 V coordination type 2 for power circuit  |
| Average impedance  | 2 mOhm - I <sub>th</sub> 50 A 50 Hz for power circuit   |
| [U <sub>i</sub> ] rated insulation voltage               | Power circuit: 600 V CSA certified<br>Power circuit: 600 V UL certified<br>Signalling circuit: 690 V conforming to IEC 60947-1<br>Signalling circuit: 600 V CSA certified<br>Signalling circuit: 600 V UL certified<br>Power circuit: 690 V conforming to IEC 60947-4-1   |
| Electrical durability                                    | 1.4 Mcycles 50 A AC-1 at U <sub>e</sub> ≤ 440 V<br>1.4 Mcycles 38 A AC-3 at U <sub>e</sub> ≤ 440 V  |
| Power dissipation per pole                               | 5 W AC-1<br>3 W AC-3  |
| Front cover  | With  |
| Mounting support   | Rail<br>Plate   |
| Standards  | CSA C22.2 No 14<br>EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508   |
| Product certifications                                   | DNV<br>LROS (Lloyds register of shipping)<br>GOST<br>RINA<br>CCC<br>CSA<br>GL<br>BV<br>UL   |
| Connections - terminals                                  | Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> flexible with cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> flexible without cable end<br>Control circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> flexible without cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> flexible with cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> solid without cable end<br>Control circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> solid without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 2.5...10 mm <sup>2</sup> flexible without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 2.5...10 mm <sup>2</sup> flexible without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...10 mm <sup>2</sup> flexible with cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1.5...6 mm <sup>2</sup> flexible with cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1.5...10 mm <sup>2</sup> solid without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 2.5...10 mm <sup>2</sup> solid without cable end |
| Tightening torque  | Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2  |
| Operating time   | 4...19 ms opening<br>12...22 ms closing   |
| Safety reliability level                                 | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1<br>B10d = 2000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1   |
| Mechanical durability                                    | 15 Mcycles  |
| Maximum operating rate                                   | 3600 cyc/h 60 °C  |

## Complementary

|                                 |  |
|---------------------------------|--|
| Coil technology                 | Without built-in suppressor module   |
| Control circuit voltage limits  | Drop-out: 0.3...0.6 Uc AC 50/60 Hz (at 60 °C)<br>Operational: 0.8...1.1 Uc AC 50 Hz (at 60 °C)<br>Operational: 0.85...1.1 Uc AC 60 Hz (at 60 °C) |
| Inrush power in VA              | 70 VA 60 Hz cos phi 0.75 (at 20 °C)<br>70 VA 50 Hz cos phi 0.75 (at 20 °C)   |
| Hold-in power consumption in VA | 7.5 VA 60 Hz cos phi 0.3 (at 20 °C)<br>7 VA 50 Hz cos phi 0.3 (at 20 °C)   |
| Heat dissipation                | 2...3 W at 50/60 Hz  |
| Auxiliary contacts type         | type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1<br>type mirror contact 1 NC conforming to IEC 60947-4-1                         |
| Signalling circuit frequency    | 25...400 Hz  |
| Minimum switching current       | 5 mA for signalling circuit  |
| Minimum switching voltage       | 17 V for signalling circuit  |
| Non-overlap time                | 1.5 ms on de-energisation between NC and NO contact<br>1.5 ms on energisation between NC and NO contact  |
| Insulation resistance           | > 10 MOhm for signalling circuit   |

## Environment

|   |   |
|---|---|
| IP degree of protection                               | IP20 front face conforming to IEC 60529   |
| Protective treatment                                  | TH conforming to IEC 60068-2-30   |
| Pollution degree                                      | 3   |
| Ambient air temperature for operation                 | -5...60 °C  |
| Ambient air temperature for storage                   | -60...80 °C   |
| Permissible ambient air temperature around the device | -40...70 °C at Uc   |
| Operating altitude                                    | 3000 m without  |
| Fire resistance                                       | 850 °C conforming to IEC 60695-2-1  |
| Flame retardance                                      | V1 conforming to UL 94  |
| Mechanical robustness                                 | Vibrations contactor open: 2 Gn, 5...300 Hz<br>Vibrations contactor closed: 4 Gn, 5...300 Hz<br>Shocks contactor closed: 15 Gn for 11 ms<br>Shocks contactor open: 8 Gn for 11 ms |
| Height  | 85 mm   |
| Width   | 45 mm   |
| Depth   | 92 mm   |
| Net weight  | 0.38 kg   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End of Life Information</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---