

192A.CPE HIGH-PERFORMANCE DIAGONAL CUTTERS



Standards :

NF ISO 5749, ISO 5749, DIN ISO 5749, ASME B107.500

Description :

- New head design to increase durability and cutting capacity
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 192A.16CPE : 2.0mm 210 kg/mm² - 192A.18CPE : 2.2mm 205 kg/mm² - 192A.20CPE : 2.5mm 200 kg/mm² • High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort. • High durability Carbon alloy steel, with induction hardened cutting edges. • Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal length) • Chrome finish for corrosion resistance

References :

	B [MM]	B1 [MM]	C [MM]	D MAXI [MM]	E [MM]	L [MM]	[G]
192A.18CPE	26,0	18	20,0	2,2	11,0	180	260
192A.20CPE	28,0	22	22,0	2,5	11,5	200	320
192A.16CPE	24,0	15	18,0	2,0	10,0	160	200