



TE Internal #: ESB201N00320500000  
 Standard Circular Connectors, Cable-to-Cable, Power, Cable Mount (Free-Hanging), Electrodeposited Nickel, Zinc Alloy, PBT+PA, 15 Shell Size, Shielded

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**  
 Sealable: **No**  
 Circuit Application: **Power**  
 Connector Mounting Type: **Cable Mount (Free-Hanging)**  
 Shell Plating Material: **Electrodeposited Nickel**

**Features**

**Product Type Features**

Product Type	Connector
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

**Electrical Characteristics**

Operating Voltage	63 VAC, 630 VAC
-------------------	-----------------

**Body Features**

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT+PA

**Mechanical Attachment**

Mating Retention Type	Push-Pull Self-Locking
-----------------------	------------------------



Connector Mounting Type

Cable Mount (Free-Hanging)

### Housing Features

Circular Connector Shell Size

15

### Dimensions

Cable Diameter Range

6.5 – 8.5 mm [.26 – .33 in]

### Usage Conditions

Operating Temperature Range

-20 – 130 °C [-4 – 266 °F]

### Operation/Application

Durability Rating

500 Cycles

Circuit Application

Power

Shielded

Yes

### Industry Standards

UL Flammability Rating

UL 94V-0

Approved Standards

UL

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUN 2020 (209)  
Candidate List Declared Against: JAN 2020 (205)  
SVHC > Threshold:  
Pb (3.5% in Component)  
**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability


Not reviewed for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # EKB202N00320604000  
915 EXTENSION



TE Part # EEA202N00000500000  
915 ITEC RECEPTACLE



TE Part # C0-0258-000-000  
POSITIONING INSERT FOR 1 MM CONTACTS



TE Part # C0-0201-000-000  
CRIMPING TOOL MID-SIZE



TE Part # C0-0235-000-000  
DIGITAL CRIMPING TOOL, SMALL

## Customers Also Bought




TE Part #661269-000  
TXR21AB00-1605AI



TE Part #ZPF000000000001261  
097-0267-16 A1267



TE Part #1617147-5  
JMGAP-26P = M39016/17-030P



TE Part #358279-000  
382C312-50-01-0



TE Part #ZPF0000000000007174  
983-ORS 08-98 PN



TE Part #YAFD56-14-15SWC019  
PLUG ASSY



TE Part #CX1369-000  
BSTS-13X4FR/NM



TE Part #CS8624-000  
BSTS-15X4FR/NM



## Documents

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_ESB201N00320500000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_ESB201N00320500000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_ESB201N00320500000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[ESB201N00320500000](#)

English

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English