

Note: This datasheet may be out of date Please download the latest datasheet of LQH43PH100M26# from the official website of Murata Manufacturing Co., Ltd. m/en/products/productdetail?partno=LQH43PH100M26%23

LQH43PH100M26#

"#" indicates a package specification code.

Size code 1812(4532)in inch(in mm), 125°⊂ Operation Available

3.2±0.2


3.2±0.2


(in mm)



< List of part numbers with package codes > LQH43PH100M26K LQH43PH100M26L











When rated current is applied to the products, inductance will be within ±30% of nominal inductance value. When rated current is applied to the products, the temperature rise caused by self-generated heat shall be limited to 40°C max. Keep the temperature (ambient temperature plus selfgeneration of heat) under 125°C.

1 of 5

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date. Please download the latest datasheet of LQH43PH100M26# from the official website of Murata Manufacturing Co., Ltd. http://www.murata.com/en/products/productdetail?partno=LQH43PH100M26%23

LQH43PH100M26#

"#" indicates a package specification code.

References

Rata

INNOVATOR IN ELECTRONI

Packaging	Specifications	Minimum Order Quantity
К	330Embossed Tape	2500
L	180Embossed Tape	500

Mass (typ.)	
1 piece	0.13g

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



2 of 5



Note: This datasheet may be out of date. Please download the latest datasheet of LQH43PH100M26# from the official website of Murata Manufacturing Co., Ltd. http://www.n nurata.com/en/products/productdetail?partno=LQH43PH100M26%23

LQH43PH100M26#

"#" indicates a package specification code.

Specifications

L size	4.5±0.3mm	
W size	3.2±0.2mm	
T size	2.6±0.2mm	
Size code inch (mm)	1812 (4532)	
Inductance	10µH±20%	
Inductance Test Frequency	1MHz	
Rated current (Isat) (Based on Inductance change)	1050mA	
Rated current (Itemp) (Based on Temperature rise)	1170mA(Ambient temp.85°C)620mA(Ambient temp.105°C)	
Max. of DC resistance	0.1764Ω	
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C	
Class of magnetic shield	Magnetic Resin	
Self resonance frequency (min.)	20MHz	
Operating Temperature Range(Self- temperature rise is not included)	-40°C to 105°C	
DC Resistance Intermediate Values	0.147Ω±20%	
Series	LQH43PH_26	

3 of 5

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date Please download the latest datasheet of LQH43PH100M26# from the official website of Murata Manufacturing Co., Ltd. ducts/productdetail?partno=LQH43PH100M26%23

10M

100M

2000

1G

3000


LQH43PH100M26#

"#" indicates a package specification code.

Characteristic Data

INNOVATOR IN FLECT

The charts below may show another part number which shares its characteristics.



4 of 5

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




Rata INNOVATOR IN ELECTRONIC

Product Search Data Sheet

Note: This datasheet may be out of date Please download the latest datasheet of LQH43PH100M26# from the official website of Murata Manufacturing Co., Ltd. http:/ ta.com/en/products/productdetail?partno=LQH43PH100M26%23

LQH43PH100M26#

"#" indicates a package specification code.



5 of 5

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

