


B45196H6156K409

aka T491D156K035ZT

Capacitor, tantalum, 15 uF, 10% Tol, 35V@85C, D



Dimensions (mm)

ID	Dimension	Tolerance
L	7.30	+/-0.30
W	4.30	+/-0.30
H	2.80	+/-0.30
K	1.50	+/-0.20
F	2.40	+/-0.10
S	1.30	+/-0.30
B	0.50	+/-0.15
X	0.10	ref
P	0.90	ref
R	1.00	ref
T	0.13	ref
A	3.80	ref
G	3.50	ref
E	3.50	ref

Specifications

Application:	General Purpose
Capacitance:	15 uF
Tolerance:	10%
Voltage DC @ 85C:	35V
Voltage DC @ 105C:	29V
Voltage DC @ 125C:	23V
Temperature Range:	-55/+125C
Size Code:	D
Footprint:	7343
Body Type:	Molded Chip
Packaging:	T&R
Package Quantity:	750
Termination Type:	Tin (Pb free)
Leakage Current:	5.3 uA
Dissipation Factor:	6%
Impedance @ 100kHz:	0.8 Ohm