

EPIC® H-B 16 Housings

Housing style H-B. The industry standard.



H-B 16 TSH-RO

Suitable inserts:

- EPIC® H-BS 6 see page 452
- EPIC® H-BVE 6 see page 454
- EPIC® H-DD 72 see page 441
- EPIC® H-EE 32 see page 450
- EPIC® MCR 16 see page 462
- EPIC® H-D 40 see page 439
- EPIC® H-BE 16 Screw termination see page 445
- EPIC® H-BE 16 Crimp termination see page 445
- EPIC® H-BE 16 Cage clamp see page 445



H-B 16 TG



H-B 16 TG 2X



Part number	Part	PG	M	ZW	L	L1	I2	B	B1	B4	H
H-B housing: Hood (side cable entry, bolts for single lever, high version)											
70104200	H-B 16 TSH-RO 21	21		yes	93,3			110	43	45	76
70104400	H-B 16 TSH-RO 29	29		yes	93,3			110	43	45	76
79104200	H-B 16 TSH-RO M25		25		93,3			110	43	45	76
79104400	H-B 16 TSH-RO M32		32		93,3			110	43	45	76
79104800	H-B 16 TSH-RO M40		40		93,3			110	43	45	76
H-B housing: Hood (straight cable entry, bolts for double lever)											
10080000	H-B 16 TG 21	21		yes	93,3	47,5		43	57,8	45	61
10090000	H-B 16 TG 29	29		yes	93,3	47,5		43	57,8	45	61
19080000	H-B 16 TG M25		25		93,3	47,5		43	57,8	45	61
19090000	H-B 16 TG M32		32		93,3	47,5		43	57,8	45	61
H-B housing: Hood (2 straight cable entries, bolts for double lever)											
19080500	H-B 16 TG 2xM25		2x25	yes	93,3	47,5		43	57,8	45	61

EPIC® H-B 16 Housings


Housing standard H-B T e in ustr stan ar




H-B 16 G- B

Suitable inserts:


- EPIC® H-BS 6 see page 452
- EPIC® H-BVE 6 see page 454
- EPIC® H-DD 72 see page 441
- EPIC® H-EE 32 see page 450
- EPIC® MCR 16 see page 462
- EPIC® H-D 40 see page 439
- EPIC® H-BE 16 Screw termination see page 445
- EPIC® H-BE 16 Crimp termination see page 445
- EPIC® H-BE 16 Cage clamp see page 445



H-B 16 D- B




H-B 16 G



Part number	Part	L	L1	L2	L3	L4	B	B1	B2	B3	B5	H	H1	s	d
	H-B housing: Panel mount base (single lever)														
10072900	H-B 16 G- B	93,3	111	109,5	103	113	43			32		27,8	4	50	4,3
	H-B housing: Panel mount base (cover, single lever)														
10073900	H-B 16 D- B	93,3	111	109,5	103	113	43			32	25	27,8	4	50	4,3
	H-B housing: Panel mount base (double lever)														
10072000	H-B 16 G	93,3	47,5		103	113	43	57,8	53	32		27,8	4	136,5	4,3

5.1 EPIC® CERTOSA M & PG


Kabelverschraubungen metrisch / Cable glands metric thread / Presse-étoupes pas métrique



EPIC® SM-M

Artikel part article	Art.Nr. part No. N° art.	M metric thread pas métrique	d1	d2	Kabel Ø cable Ø câble Ø	d3	Kabel Ø cable Ø câble Ø	d4	Kabel Ø cable Ø câble Ø	d5	Kabel Ø cable Ø câble Ø	S	SW mm opening of the spanner ouverture de clef	VPE packing unit condition- nement
SM-M12	71200000	12	10	5	4-6							5	12	5
SM-M16	71200100	16	13,8	3	2-4	6	5-7	9	8-10			5,5	16	5
SM-M20	71200200	20	13,9	4	3-5	7	6-8	10	9-11	13	12-13,5	6	20	5
SM-M25	71200300	25	22,6	8,5	7,5-9,5	11,5	10,5-12,5	14,5	13,5-15,5	17,5	16,5-18,5	7,5	25	5
SM-M32	71200400	32	29,6	16	15-17	19	18-20	22	21-23	25	24-26	9,5	32	5
SM-M40	71200500	40	37,6	23	22-24	26	25-27	29	28-30	32	31-33	12	40	5
SM-M50	71200600	50	47,6	30	29-31	33	32-34	36	35-37	39	38-40	14	50	5

Material / material / matière: Metall, Messing vernickelt / metal, brass, nickel plated / métallique, laiton nickelage
 Schutzart / protection class / degré de protection: IP 65 (EN60529)
 Temperaturbereich / temperature range / gamme de température: -40 °C bis +80 °C



EPIC® CM-M

Artikel part article	Art.Nr. part No. N° art.	M metric thread pas métrique	d1	d2	Kabel Ø cable Ø câble Ø	d3	Kabel Ø cable Ø câble Ø	d4	Kabel Ø cable Ø câble Ø	d5	Kabel Ø cable Ø câble Ø	S	SW mm opening of the spanner ouverture de clef	VPE packing unit condition- nement
CM-M12	71201000	12	10	5	4-6							5	15	5
CM-M16	71201100	16	13,8	3	2-4	6	5-7	9	8-10			5,5	19	5
CM-M20	71201200	20	13,9	4	3-5	7	6-8	10	9-11	13	12-13,5	6	23	5
CM-M25	71201300	25	22,6	8,5	7,5-9,5	11,5	10-12,5	14,5	13,5-15,5	17,5	16,5-18,5	7,5	28	5
CM-M32	71201400	32	29,6	16	15-17	19	18-20	22	21-23	25	24-26	9,5	36	5
CM-M40	71201500	40	37,6	23	22-24	26	25-27	29	28-30	32	31-33	12	46	5
CM-M50	71201600	50	47,6	30	29-31	33	32-34	36	35-37	39	38-40	14	55	5

Material / material / matière: Metall, Messing vernickelt / metal, brass, nickel plated / métallique, laiton nickelage
 Schutzart / protection class / degré de protection: IP 65 (EN60529)
 Temperaturbereich / temperature range / gamme de température: -40 °C bis +80 °C