

HUBER+SUHNER® DATA SHEET

Coaxial Cable: S_10162_B-11



Description

PE Foam - 50 Ohm - high screened

Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Copper clad Aluminum	Wire	3.8 mm
Dielectric	SPE (Foamed Polyethylene)		9.9 mm
Outer conductor	Copper	longitudinal Foil, 100 %	10 mm
Outer conductor	Copper	Braid, 80 %	10.8 mm
Jacket	LSFH (modified polyethylene)	RAL 9005 - bk	12.9 mm +/- 0.2
Print	HUBER+SUHNER S 10162 B-11 50 Ohm (PA no.)		

Electrical Data

Impedance	50	Ω +/- 2
Max. operating frequency	7.5	GHz
Capacitance	77	pF/m
Velocity of signal propagation	87	%
Signal delay	3.85	ns/m
Insulation resistance	$\geq 1 \times 10^8$	M Ω m
Min. screening effectiveness	>90	dB (up to 7.5 GHz)
Max. operating voltage	1.7	kV _{rms} (at sea level)
Test voltage	3.4	kV _{rms} (50 Hz/1 min)

Mechanical Data

Weight	15	kg/100 m
Min. bending radius	static	100 mm
	repeated (for max. 50 bendings)	200 mm

Environmental Data

Temperature range	-40 °C... + 85 °C
Installation temperature	-20 °C... + 60 °C
Flammability	IEC 60332-1, EN 60332-1-2, EN 50266-2-4, IEC 60332-3-24 BS 4066-3, NF C 32-070 C2
Smoke density	EN 61034-2, NF X 10-702
Halogen free	IEC 60754
Uv resistance test	ISO 4892-2A
Toxic fume	BS 6853 Annex B, NF X 70-100
2002/95/EC (RoHS)	compliant

Ordering Information

Order as S_10162_B-11

Additional Information

DIN 5510-2 and CEN/TS 45545 compliant

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Cable group S39 10 mm / 50 Ohm

HUBER+SUHNER® DATA SHEET

Coaxial Cable: S_10162_B-11



Rev.: Q

Matrix **Attenuation** [formula: $(a \cdot f^{0.5} + b \cdot f)$] **and Power CW** [formula: $(p \cdot f^{0.5})$]

Coefficients:

a=	0.0826	b=	0.0129	f _{max} =	7.5	p _{at} 1GHz =	700
	Frequency		Nom. attenuation		Nom. attenuation		Max. CW power
	(GHz)		(dB / m)		(dB / ft)		(watt)
			sea level 25° C ambient temperature		sea level 25° C ambient temperature		sea level 40° C ambient temperature
	0.4		0.06		0.018		1107
	0.8		0.08		0.024		783
	1.1		0.10		0.030		667
	1.5		0.12		0.037		572
	1.9		0.14		0.043		508
	2.3		0.15		0.046		462
	2.6		0.17		0.052		434
	3.0		0.18		0.055		404
	3.4		0.20		0.061		380
	3.8		0.21		0.064		359
	4.1		0.22		0.067		346
	4.5		0.23		0.070		330
	4.9		0.25		0.076		316
	5.3		0.26		0.079		304
	5.6		0.27		0.082		296
	6.0		0.28		0.085		286
	6.4		0.29		0.088		277
	6.8		0.30		0.091		268
	7.1		0.31		0.094		263
	7.5		0.32		0.098		256

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Industrial
9100 Herisau, Switzerland
 Phone +41 (0)71 353 41 11
 Fax +41 (0)71 353 45 90
 www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions