

ENERGIZER ECRN2016 Industrial


Lithium Coin



General Information

Classification: "Lithium Coin"
Chemical System: Lithium / Manganese Dioxide (Li/MnO₂)
Designation: ANSI / NEDA-5000LC, IEC-CR2016
Nominal Voltage: 3.0 Volts
Typical Capacity: 100 mAh (to 2.0 volts)
 (Rated at 30K ohms at 21°C)
Typical Weight: 1.9 grams (0.07 oz.)
Typical Volume: 0.5 cubic centimeters (0.03 cubic inch)
Max Rev Charge: 1 microampere
Energy Density: 122 milliwatt hr/g, 464 milliwatt hr/cc
Typical Li Content: 0.036 grams (0.0013 oz.)
Operating Temp: -30C to 60C
Self Discharge: ~1% / year

Industry Standard Dimensions mm (inches)



Simulated Application test

Typical Performance at 21°C (70°F)

Schedule:	Typical Drains: at 2.9V (mA)	Load (ohms)	Cutoff 2.0V (hours)
Continuous	0.1	30,000	1040

Typical Discharge Characteristics

Load: 30K ohms - Continuous
 Typical Drain @ 2.9V: 0.097 mA




Internal Resistance Characteristics

Pulse Test at 21°C (70°F)

Bkgnd Drain: Continuous
 30K ohms
 0.1 mA @2.9V

Pulse Drain: 2 seconds X 12 times/day
 400 ohms
 6.8 mA @2.7V



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
Contents herein do not constitute a warranty and are for reference only.