

USB Type A to USB Type B Cable Assembly



Specifications

Material

Connector : Housing: Thermoplastic, Glass fiber fill, UL94V-0
 Contact: Phosphor Bronze, Gold Plating on Contact Interface
 Shell: Steel, Tin-Lead Plating over Copper Underplating

Cable : USB Standard Full Speed type, UL94V-0
 Overmold : PVC, UL94V-0

Electrical

Voltage : 30V AC
 Current : 1A Max. per Contact


Mechanical

Random Vibration : No Discontinuity of 1µS or longer Duration
 Physical Shock : No Discontinuity of 1µS or longer Duration
 Insertion Force : 4kg Max.
 Withdrawal Force : 1kg to 4kg

Environmental

Thermal Shock : 10 Cycle -55°C to +85°C
 Colour : Off White

Diagram



Part Number Table

Description	Part Number
USB Cable, Type A Plug to Type B Plug, 5m, USB 2.0, White	SPC4801

Dimensions : Inches (Millimetres)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

