

## TECHNICAL DATA SHEET

Part#: 7-TA

**Tweezers - 4 Star Curved Very Fine Point - Titanium Alloy**  
The curved points provide excellent visibility. Excellent for soldering applications. Light weight

The 7-TA titanium alloy tweezers are designed for high temperature applications (806°F (430°C)). They are also very light and have high resistance to most acids. They have zero magnetic retentivity and solder will not stick to them. They feature our hardest points.

• Precision Level	★★★★
• Material	Titanium Alloy
• Surface Resistivity	Conductive
• Shape	Curved
• Tip Size	.0094" x .003" (.235mm x .075mm)
• Tip Angle	55°
• Tip Length	
• Body Width	0.393" (9.83mm)
• Body Height	.06" (1.5mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	1
• UPC	662847003165
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Titanium



C.T.M.  
Critical Tip Measurements  
(Tip Width and Thickness of one point)

