



Surface mounting enclosure, stainless steel, 3 mounting locations



**Part no.** M22-I3M/SS  
**Catalog No.** 118460  
**Alternate Catalog No.** M22-I3M-SS

### Delivery program

|                              |  |      |   |
|------------------------------|--|------|---|
| Basic function accessories   |  |      | Surface mounting enclosure  |
| Housing                      |  |      | Stainless steel   |
|                              |  |      | With high-grade steel screws<br>With mounting tabs on the sides   |
| Number of locations          |  | Qty. | 3   |
| <b>Cable entry knockouts</b> |  |      |   |
| Cable entry                  |  |      | -   |
| Degree of Protection         |  |      | IP66, IP67, IP69  |
| Connection to SmartWire-DT   |  |      | no  |
| For use with                 |  |      | 3 x Ø 22.5  |
| For use with                 |  |      | (Illuminated) pushbuttons<br>(Illuminated) selector switches<br>Key-operated pushbuttons<br>Indicator light<br>controlled stop/emergency-stop buttons with yellow label |

### Technical data

#### General

|                      |  |  |                  |
|----------------------|--|--|------------------|
| Degree of Protection |  |  | IP66, IP67, IP69 |
|----------------------|--|--|------------------|

### Design verification as per IEC/EN 61439

|  |  |  |  |
|--|--|--|--|
| IEC/EN 61439 design verification   |  |  |  |
| 10.2 Strength of materials and parts   |  |  |  |
| 10.2.2 Corrosion resistance  |  |  | Meets the product standard's requirements.   |
| 10.2.3.1 Verification of thermal stability of enclosures   |  |  | Meets the product standard's requirements.   |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |  |  | Meets the product standard's requirements.   |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |  |  | Meets the product standard's requirements.   |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |  |  | Please enquire   |
| 10.2.5 Lifting   |  |  | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.6 Mechanical impact   |  |  | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.7 Inscriptions  |  |  | Meets the product standard's requirements.   |
| 10.3 Degree of protection of ASSEMBLIES  |  |  | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.4 Clearances and creepage distances   |  |  | Meets the product standard's requirements.   |
| 10.5 Protection against electric shock   |  |  | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.6 Incorporation of switching devices and components   |  |  | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.7 Internal electrical circuits and connections  |  |  | Is the panel builder's responsibility.   |
| 10.8 Connections for external conductors   |  |  | Is the panel builder's responsibility.   |
| 10.9 Insulation properties   |  |  |  |
| 10.9.2 Power-frequency electric strength   |  |  | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage   |  |  | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material   |  |  | Is the panel builder's responsibility.   |
| 10.10 Temperature rise   |  |  | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating   |  |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility  |  |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function  |  |  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## Technical data ETIM 7.0

|  |  |    |                          |
|--|--|----|--------------------------|
| Low-voltage industrial components (EG000017) / Enclosure for control circuit devices (EC000200)  |  |    |                          |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Housing for command and alarm devices<br>(ec1@ss10.0.1-27-37-12-05 [AKF023014]) |  |    |                          |
| Number of command positions  |  |    | 3                        |
| Construction type housing  |  |    | Surface mounting housing |
| Material housing   |  |    | Stainless steel          |
| Material quality housing   |  |    | Other                    |
| Diameter openings  |  | mm | 22.5                     |
| Colour housing cover   |  |    | Grey                     |
| Degree of protection (IP)  |  |    | IP67/IP69K               |
| Degree of protection (NEMA)  |  |    | 4X                       |
| Width  |  | mm | 105                      |
| Height   |  | mm | 84                       |
| Depth  |  | mm | 220                      |