



MASTER VALUE LEDspot MV

MASTER LED spot VLE DT 3.7-35W GU10 927 36D

Delivering a warm, halogen-like accent beam, MASTER VALUE LEDspot MV is a perfect for spot lighting. Thanks to its high CRI, it realizes more natural colors, enabling cozy and comfortable ambience for residential, hospitality and emphasize the beauty of merchandise in retail. These LEDspots have the familiar look and feel of glass spots, keeping the classic beauty of glass spots and adding the strong performance from LED technology. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers.

Product data

General Information	
Cap-Base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	3.7-35W
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	260 lm
Luminous Intensity (Nom)	500 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	78.38 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Luminous Flux in 90° Cone (Rated)	260 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	3.7 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Yes

MASTER VALUE LEDspot MV

Approval and Application


Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

Product Data

Full product code	871869670809500
Order product name	MASTER LED spot VLE DT 3.7-35W GU10 927 36D

EAN/UPC - Product	8718696708095
Order code	929001350002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001350002
Net Weight (Piece)	0.038 kg


Dimensional drawing




GU10 230V4W-35W230lm36D 22-2700K GU10Dim

Product	D	C
MASTER LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm

Photometric data




MASTER LEDspotMV GU10 922-927 36D



MASTER LEDspotMV 35W GU10 922-927 36D

MASTER VALUE LEDspot MV


Photometric data




General Parameters 43 Photo Lighting 8 11 Page 117

MASTER LEDspotMV 35W GU10 922-927 36D

Lifetime



MASTER LEDspotMV GU10 922-927 36D



MASTER LEDspotMV GU10 922-927 36D

