

TECHNICAL DATA SHEET

Part#: 9241SL

Cutters - Medium Oval Head -★★★★- Carbon Steel - Slim Line - Black Oxide Coated

The 9241SL optimum flush new and improved Lazer Line[®] medium SLIM LINE oval head cutters feature BLACK OXIDE FINISH and a smaller frame with new molded grip. They are made of AISI 52/100 carbon tool steel with induction hard cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action. MOLDED Grips - ESD safe (10^8 ohms/sq.)

• Precision Level	★★★★
• Material	Carbon
• Surface Resistivity	10^{10} ohms/sq
• Shape	Round Head
• Type of Cut	Optimum Flush
• Group	Cutting Tools
• Cutting Capacity	36 - 18 AWG / .005 - .040" / .13 - 1 mm
• Blade Angle	16°
• Blade Length	.266" (6.65mm)
• Body Width	0.375" (9.38mm)
• Body Height	.225" (5.63mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	3
• UPC	662847014024
• Schedule B	8203.20.60.60
• ECCN	EAR99
• UNSPSC Code	27111511
• Country of Origin	USA

