

GCM1555C1H2R7WA16#

“#” indicates a package specification code.



< List of part numbers with package codes >

GCM1555C1H2R7WA16D

GCM1555C1H2R7WA16W

GCM1555C1H2R7WA16J

Appearance & Shape



References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|-------------------------|---------------------------|
| D | 180mm Paper Tape | 10000 |
| W | 180mm Paper Tape (W8P1) | 20000 |
| J | 330mm Paper Tape | 50000 |

| Mass (typ.) | |
|-------------|-------|
| 1 piece | 1.6mg |
| φ180mm Reel | 118g |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GCM1555C1H2R7WA16#

“#” indicates a package specification code.



Specifications

| | |
|--|----------------|
| Length | 1.0±0.05mm |
| Width | 0.5±0.05mm |
| Thickness | 0.5±0.05mm |
| Capacitance | 2.7pF ±0.05pF |
| Distance between external terminals g | 0.3mm min. |
| External terminal size e | 0.15 to 0.35mm |
| Operating Temperature Range | -55°C to 125°C |
| Rated Voltage | 50Vdc |
| Size code in inch(mm) | 0402 (1005M) |
| TC | 0±30ppm/°C |
| Temperature characteristics (complied standard) | C0G(EIA) |
| Temperature range of temperature characteristics | 25°C to 125°C |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


GCM1555C1H2R7WA16#

"#" indicates a package specification code.




Characteristic Data

The charts below may show another part number which shares its characteristics.



GCM1555C1H2R7WA16 |Z| DCOV, 25degC



GCM1555C1H2R7WA16 R DCOV, 25degC



GCM1555C1H2R7WA16 C-DC bias capchange, 25.0degC, AC1V



GCM1555C1H2R7WA16 C-AC Voltage capchange, DCOV, 25.0d


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GCM1555C1H2R7WA16#


“#” indicates a package specification code.

Temperature Characteristics



■ GCM1555C1H2R7WA16 C-Temp. capchange, DCOV, AC1Vrms

S Parameter S21



■ GCM1555C1H2R7WA16 S21 DCOV, 25degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.