

## Twist-Lock® Devices

20A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding

Spring Termination Single Flush Receptacle

# HUBBELL

### Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

### Ordering Information

Description	Device Color	UPC	Catalog Number
Nylon face, back wire	Black	783585788500	HBL2510ST

### Listings

Listed to UL 498  
Certified to CSA C22.2 No.42

### Specifications

Face	Nylon
Base	Nylon
Contacts	Brass
Spring	Steel
Mounting Strap	Brass

### Performance

#### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

#### Mechanical

Terminal Accommodation	Solid/Stranded #14 AWG to #12 AWG
Terminal Identification	Terminals identified in accordance with UL 498
Ground Wire	#12 AWG Stranded, 5" long

#### Environmental

Flammability	V2 or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



20A 3ØV  
120/208V AC  
NEMA L21-20R  
UL/CSA  
2 HP



### Accessories

Plug	HBL2511
Wallplate or Weatherproof Cover	1.60" Opening
Switched Enclosure	SETL3

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

