



HX-CT

TE Internal #: EL8211-000

HX-CT, Printable Tubing, Continuous Printable Tubing Type, Low Fire Hazard Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio, Yellow

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE LOW FIRE HAZARD HX-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Low Fire Hazard**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **Yellow**

Supplied Inner Diameter: **38.1 mm [1.5 in]**

[All CONTINUOUS TUBE LOW FIRE HAZARD HX-CT \(18\)](#)

Features

Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	Low Fire Hazard

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	Yellow

Dimensions

Supplied Inner Diameter	38.1 mm[1.5 in]
Recovered Inside Diameter	19 mm[.75 in]
Compatible Cable Diameter Range	19 – 30.48 mm[.75 – 1.2 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer
---------------------	--



Product Ribbon Matrix

Printer Technology

Thermal Transfer

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUL 2021 (219)
 Candidate List Declared Against: JAN 2021 (211)
 SVHC > Threshold:
 Not Yet Reviewed

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts








Also in the Series | HX-CT



Customers Also Bought



Documents

Product Drawings

[HX-CT-40M-38.1-OUT-4](#)

English

Datasheets & Catalog Pages

[HX-CT, Low Fire Hazard Continuous Heat Shrink Identification Tube](#)

English



Product Specifications

[HX - LFH Heat Shrink Sleeving](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English