

# TECHNICAL DATA SHEET


RoHS  
Compliant

## MICROPHONE CABLE

### APPLICATION

Professional, balanced (2-core) or unbalanced (single-core) microphone cable suitable for use in audio applications.

## MODELS: PELB0584- PELB0585



### ELECTRICAL CHARACTERISTICS

Rated Temperature: 60°C

Conductor Resistance (Max. @ 20°C): 88.03Ω/km (balanced), 88.24Ω/km (unbalanced),

### CONSTRUCTION

Model	PELB0584	PELB0585
Type	Balanced	Unbalanced
Core Insulation	PE	
Core Insulation Colours	Red White	Red
Filler	Cotton Yarn	N/A
Screen (BC OFC)	80/0.10mm	30/0.10mm
Screen Coverage	100%	57%
Covering	PE	N/A
Covering Colour	Black	N/A
Jacket	PVC	
Jacket Colour	Black	

### DIMENSIONS

Cores	Conductors	Overall Dia.	Length	Model
2	20/0.12mm	6.50mm	100m	PELB0584
1		5.00mm		PELB0585

**Important Notice:** This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.