

ZHD-CT

TE Internal #: EL8111-000

ZHD-CT, Printable Tubing, Continuous Printable Tubing Type, Fluid

Resistant & Low Fire Hazard Printable Tubing Grade

View on TE.com >



Identification & Labeling > Printable Tubing > ZHD-CT LFH & FLUID RESISTANT TUBE



Printable Tubing Type: Continuous

Printable Tubing Grade: Fluid Resistant & Low Fire Hazard

Printable Tubing Shrink Ratio: 2:1
Primary Product Color: White

Supplied Inner Diameter: 2.4 mm [.094 in]

All ZHD-CT LFH & FLUID RESISTANT TUBE (18)

Features

Product Type Features

| Product Type Features | |
|---------------------------------|--|
| Printable Tubing Type | Continuous |
| Printable Tubing Grade | Fluid Resistant & Low Fire Hazard |
| Body Features | |
| Printable Tubing Shrink Ratio | 2:1 |
| Primary Product Color | White |
| Dimensions | |
| Supplied Inner Diameter | 2.4 mm[.094 in] |
| Recovered Inside Diameter | 1.2 mm[.047 in] |
| Compatible Cable Diameter Range | 1.2 – 1.9 mm[.05 – .075 in] |
| Usage Conditions | |
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
| Operation/Application | |
| Recommended Ribbon | See TE Document 411-121005 the Printer Product Ribbon Matrix |
| | |

See TE Document 411-121005 the Printer

Product Ribbon Matrix

Printer/Label Features

Recommended Printer



| Printer Technology | Thermal Transfer |
|--------------------|------------------|
| Packaging Features | |
| Packaging Quantity | 50 |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU | Compliant |
|---|--|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts


















Also in the Series | ZHD-CT



Customers Also Bought









TE Part #6787634001 ZH-100-3/8-0-SP





TE Part #176819-000 B-150-11



TE Part #270225-000 B-150-07



TE Part #4-1768018-2 EET-1325P-4

Documents

Product Drawings
ZHD-CT-50M-2.4-OUT-9

English

Datasheets & Catalog Pages

ZHD-CT, Continuous Zero Low Fire Hazard, Diesel Resistant Heat Shrink Identification Tube

English

ZHD-CT, Printable Tubing, Continuous Printable Tubing Type, Fluid Resistant & Low Fire Hazard Printable Tubing Grade



Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English