


ATWPH1X100CK | ATWPH.CK - PROTWIST® SHOCK screwdrivers for Phillips® screws




Standards:

NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600

Description:

- Impact Zone with Steel Strike - hexagonal blade with 73MO steel.
- Hexagonal blade with shoulder to take a wrench.
- Extra-long blade for use in confined spaces.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Golden electroplated Tip - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.

	ATWPH1X100CK
Diameter [mm]	30.0
Diameter D1 [mm]	5.0
Length L1 [mm]	100.0
Length L [mm]	209.0
Length L2 [mm]	109.0
Weight [g]	70.0
Phillips Tip Number ["]	PH1