


- **Ultra-wide 12:1 input voltage range: 9–75, 14–160 VDC**
- **EN 50155 and EN 61373 certified**
- **Encapsulated quarter-brick (2.3"x1.45"x0.5") package**
- **Extended holdup time with lowest capacitor volume**
- **EN 45545-2 fire behavior**
- **-40°C to +85°C operating temperature**
- **Up to 3'000 VAC I/O-isolation**
- **Remote on/off and trim function**
- **Adjustable undervoltage lockout (UVLO), short-circuit protection (SCP), overvoltage protection (OVP) and overtemperature protection (OTP)**
- **3-year product warranty**



The TEP 100UIR is a series of high-performance 100 Watt DC/DC converters with an ultra-wide 12:1 input voltage range. The TEP 100UIR comes in a compact, fully encapsulated quarter-brick (2.3"x1.45"x0.5") package for highest reliability. The ultra-wide input voltage range lets system builders reduce the number of design channels where otherwise multiple input voltage configurations would be required. Thanks to its dedicated holdup circuit, the TEP 100UIR complies with extended holdup-time requirements without the need for bulky capacitors. The TEP 100UIR is EN 50155 certified for rolling stock applications, EN 61373 certified for mechanical shock and vibration and EN 45545-2 certified for fire behavior. It comes with IEC/EN/UL 62368-1 safety approvals.

Models				
Order Code	Input Voltage Range	Output Voltage nom.	Output Current max.	Efficiency typ.
TEP 100-3611UIR	9 - 75 VDC (36 VDC nom.)	5 VDC	20'000 mA	88 %
TEP 100-3612UIR		12 VDC	8'350 mA	88 %
TEP 100-3613UIR		15 VDC	6'700 mA	89 %
TEP 100-3615UIR		24 VDC	4'200 mA	88 %
TEP 100-3618UIR		48 VDC	2'100 mA	90 %
TEP 100-7211UIR	14 - 160 VDC (110 VDC nom.)	5 VDC	20'000 mA	88 %
TEP 100-7212UIR		12 VDC	8'350 mA	88 %
TEP 100-7213UIR		15 VDC	6'700 mA	88 %
TEP 100-7215UIR		24 VDC	4'200 mA	88 %
TEP 100-7218UIR		48 VDC	2'100 mA	89 %

Options	
TEP-HS2	- Optional Heat Sink: www.tracopower.com/products/tep-hs2.pdf
TEP-HS4	- Optional Heat Sink: www.tracopower.com/products/tep-hs4.pdf
on demand (backorder with MOQ non stocking item)	- Optional Heat Sink with large profile: www.tracopower.com/products/tep-hs3.pdf - Optional Heat Sink with large profile: www.tracopower.com/products/tep-hs5.pdf - Optional model with 28 VDC / 3'600 mA Output and 9 - 75 VDC Input - Optional model with 53 VDC / 1'920 mA Output and 9 - 75 VDC Input - Optional model with 28 VDC / 3'600 mA Output and 14 - 160 VDC Input - Optional model with 53 VDC / 1'920 mA Output and 14 - 160 VDC Input

Input Specifications

Input Current	- At no load	36 Vin models: 20 mA typ. 110 Vin models: 15 mA typ.
Surge Voltage		36 Vin models: 100 VDC max. (1 s max.) 110 Vin models: 185 VDC max. (1 s max.)
Start-up Voltage		36 Vin models: 8.1 VDC min. / 8.5 VDC typ. / 9 VDC max. 110 Vin models: 12 VDC min. / 13.2 VDC typ. / 14 VDC max. (These are the Start-up Voltage values without an external resistor between the UVLO and -Vin pin. With an external resistor between these pins, the Start-up Voltage can be widely adjusted, see application note: www.tracopower.com/overview/tep100uir)
Under Voltage Lockout		36 Vin models: 7.3 VDC min. / 7.7 VDC typ. / 8.1 VDC max. 110 Vin models: 10 VDC min. / 11 VDC typ. / 12 VDC max. (These are the Shutdown Voltage values without an external resistor between the UVLO and -Vin pin. With an external resistor between these pins, the Shutdown Voltage can be widely adjusted, see application note: www.tracopower.com/overview/tep100uir)
Recommended Input Fuse		36 Vin models: 20'000 mA (fast acting) 110 Vin models: 13'000 mA (fast acting) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type (By the use of following input capacitor, the input ripple can be further reduced: 36 Vin models: 220 μ F / 100 V KY 110 Vin models: 150 μ F / 200 V KXJ)

Output Specifications

Output Voltage Adjustment		-20% to +10% (By external trim resistor) See application note: www.tracopower.com/overview/tep100uir Output power must not exceed rated power!
Voltage Set Accuracy		$\pm 1\%$ max.
Regulation	- Input Variation (Vmin - Vmax) - Load Variation (0 - 100%)	0.1% max. 0.1% max.
Ripple and Noise (20 MHz Bandwidth)		5 Vout models: 75 mVp-p typ. (w/ 10 μ F // 4.7 μ F) 12 Vout models: 100 mVp-p typ. (w/ 22 μ F) 15 Vout models: 100 mVp-p typ. (w/ 22 μ F) 24 Vout models: 200 mVp-p typ. (w/ 4.7 μ F) 28 Vout models: 200 mVp-p typ. (w/ 4.7 μ F) 48 Vout models: 300 mVp-p typ. (w/ 2.2 μ F) 53 Vout models: 300 mVp-p typ. (w/ 2.2 μ F)
Capacitive Load		5 Vout models: 40'000 μF max. 12 Vout models: 7'000 μF max. 15 Vout models: 4'500 μF max. 24 Vout models: 1'800 μF max. 28 Vout models: 1'300 μF max. 48 Vout models: 430 μF max. 53 Vout models: 370 μF max.
Minimum Load		Not required
Temperature Coefficient		$\pm 0.02\%$/K max.
Hold-up Time		10 ms min. (with external capacitor, see application note for BUS connection: www.tracopower.com/overview/tep100uir)

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

Short Circuit Protection	Continuous, Automatic recovery
Output Current Limitation	110 - 130% of I _{out} max.
Overvoltage Protection	120 - 135% of V _{out} nom.
Transient Response	- Response Deviation - Response Time
	25% typ. (25% Load Step) 250 µs typ. (25% Load Step)

Safety Specifications

Safety Standards	- IT / Multimedia Equipment - Railway Applications - Certification Documents	EN 62368-1 IEC 62368-1 UL 62368-1 EN 50155 www.tracopower.com/overview/tep100uir
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI Emissions	- Conducted Emissions - Radiated Emissions	EN 50121-3-2 (EMC for Rolling Stock) EN 55032 class A (with external filter) EN 55032 class B (with external filter) EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	External filter proposal:	www.tracopower.com/overview/tep100uir
EMS Immunity	- Electrostatic Discharge - RF Electromagnetic Field - EFT (Burst) / Surge - Conducted RF Disturbances - PF Magnetic Field	EN 50155 (Railway Applications) EN 50121-3-2 (EMC for Rolling Stock) EN 55024 (IT Equipment) Air: EN 61000-4-2, ±8 kV, perf. criteria A Contact: EN 61000-4-2, ±6 kV, perf. criteria A EN 61000-4-3, 20 V/m, perf. criteria A EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±1 kV, perf. criteria A Ext. input component: 220 µF / 100 V KY (36 V _{in} models) 150 µF / 200 V KXJ (110 V _{in} models) Continuous: EN 61000-4-6, 10 V _{rms} , perf. criteria A 1 s: EN 61000-4-8, 100 A/m, perf. criteria A EN 61000-4-8, 1000 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +105°C +105°C max. -55°C to +125°C
Power Derating	- High Temperature	See application note: www.tracopower.com/overview/tep100uir
Over Temperature Protection Switch Off	- Protection Mode - Measurement Point	110°C typ. (Automatic recovery at 95°C typ.) Base-Plate
Cooling System		Forced air cooling (with external fan, 400 LFM)
Sense Function		10% max. of V _{out} nom. (If sense function is not used, sense pins must be connected to corresponding polarity output pins)
Remote Control	- Voltage Controlled Remote - Off Idle Input Current - Remote Pin Input Current	On: 3.0 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit 3 mA typ. -0.5 to 1.0 mA
Altitude During Operation		5'000 m max.
Switching Frequency		160 - 200 kHz (PWM) 180 kHz typ. (PWM)

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

Insulation System		Reinforced Insulation (110 Vin models) Basic Insulation (36 Vin models)
Working Voltage (rated)		220 VAC
Isolation Test Voltage	- Input to Output, 60 s	3'000 VAC (110 Vin models) 2'250 VDC (36 Vin models)
	- Input to Case, 60 s	1'500 VAC (110 Vin models) 1'600 VDC (36 Vin models)
	- Output to Case, 60 s	1'500 VAC (110 Vin models) 1'600 VDC (36 Vin models)
Creepage	- Input to Output	3.2 mm min.
Clearance	- Input to Output	3 mm min.
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	1'000 pF max.
Reliability	- Calculated MTBF	420'800 h (MIL-HDBK-217F, ground benign)
Environment	- Vibration	MIL-STD-810F EN 61373 7.6 g, 3 axis, 60 min, 20-2000 Hz
	- Mechanical Shock	MIL-STD-810F EN 61373 50 g, 3 axis, 11 ms
	- Thermal Shock	MIL-STD-810F -55°C to +125°C, 72 cycles, 30 min each EN 50155
Housing Material		Alu base-plate w. plastic case
Isolation Frame Material		Non-conductive black Plastic (UL94 V-0 rated)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper
Pin Foundation Plating		Copper (1 - 1.5 μm)
Pin Surface Plating		Nickel (4 - 6 μm), matte
Connection Type		THD (Through-Hole Device)
Weight		64 g
Thermal Impedance		8.3 K/W
Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant
	- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule). The SCIP number is provided on request.)
	- Flammability (EN 45545-2)	www.tracopower.com/info/en45545-declaration.pdf


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tep100uir

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

Outline Dimensions



Pin (4, 8): 1.5 (0.06)
Pin (other): 1.0 (0.04)

Pinout	
Pin	Signal
1	-Vin (GND)
2	Remote On/Off
3	+Vin (Vcc)
4	-Vout
5	-Sense
6	Trim
7	+Sense
8	+Vout
9	Bus
10	UVLO