

KERN EMB 3000-1S



The space miracle - stackable school balance for experiment-based teaching, now also as a high-resolution variant



Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readability [d]:	100 mg
Recommended adjusting weight:	3 kg (F2)
Repeatability:	200 mg
Resolution:	30000
Stabilisation time under laboratory conditions:	2,500 s
Tare range:	3 kg
Warm up time:	2 h
Weighing capacity [Max]:	3 kg
Weighing system:	Strain gauge
Weighing units:	g dwt oz ozt

Display

Display digit height (large):	1,500 cm
-------------------------------	----------

Functions

Capacity display:	yes
-------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	2x1.5 V AA
Charging time:	10 h
Mains adapter:	Mains adapter external
Operating time:	35 h
Operating time (Backlight off):	50 h

Services (optional)

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	School balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	230 x 170 x 55 mm
Gross weight:	505 g
Net weight:	358 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	145 x 205 x 40 mm
Material weighing plate:	Plastic
Weighing surface (d):	120

Piktogramme

STANDARD



OPTION

