

KERN EOE30K-2



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



Measuring system

Adjustment options:	External calibration
Linearity:	20 g
Readability [d]:	10 g
Recommended adjusting weight:	20 kg (M2)
Repeatability:	10 g
Resolution:	3500
Stabilisation time under laboratory conditions:	2,500 s
Tare range:	35 kg
Warm up time:	10 min
Weighing capacity [Max]:	35 kg
Weighing system:	Strain gauge
Weighing units:	lb kg PCS

Display

Display digit height (large):	2,500 cm
-------------------------------	----------

Functions

Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	4x1.5 V AA
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time:	100 h

Services (optional)

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Category

Brand:	KERN
Category:	Balances

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	365 x 365 x 160 mm
Gross weight:	5,100 kg
Net weight:	3,900 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	2 m
Casing material:	plastic
Dimensions of display device (WxDxH):	235 x 114 x 51 mm
Dimensions of weighing plate (WxDxH):	315 x 305 x 57 mm
Material weighing plate:	Steel lacquered
Wall mount:	yes

Piktogramme

STANDARD



OPTION

