

# KERN EW620-3NM

The classic balance with robust tuning fork measuring system



## Measuring system

Adjustment options:	External calibration
Linearity:	3 mg
Minimum weight (USP):	2 g
Readability [d]:	1 mg
Recommended adjusting weight:	500 g (E2)
Repeatability:	1 mg
Resolution:	620000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	4 h
Weighing capacity [Max]:	620 g
Weighing units:	tl (HK) tol g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) ozt

## Display

Display digit height (large):	1,700 cm
-------------------------------	----------

## Counting

Counting resolution:	620000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

## Functions

Capacity display:	yes
Counting function:	yes
Percentage determination:	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

## Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH
Operating time (Backlight off):	32 h
Operating time (Backlight on):	12 h
Rechargeable battery:	Rchrg. battery optional

## Services (optional)

DAkkS Certificate:	963-103
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 325 x 220 mm
Gross weight:	2,960 kg
Net weight:	1,365 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions draft shield (WxDxH):	174 x 144 x 105 mm
Dimensions housing (WxDxH):	182 x 235 x 75 mm
Draft shield optional:	yes
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	158 x 130 x 78 mm
Weighing surface (d):	118


# KERN EW620-3NM



The classic balance with robust tuning fork measuring system

## Piktogramme

### STANDARD



### OPTION



### FACTORY

