

# KERN HFM5T0.5



Robust industrial crane scale with bright LED display for optimum reading in unfavourable ambient conditions



Tare range:	-5 t
Warm up time:	30 min
Weighing capacity [Max]:	5 t
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height (large):	3 cm
-------------------------------	------

## Functions

Data hold function:	yes
---------------------	-----

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

## Power supply

Battery:	1x12V Type 23A
Charging time:	14 h
Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time (Backlight off):	50 h
Operating time (Backlight on):	50 h

## Services (optional)

Adjustment at the location of installation:	961-252
DAkkS Certificate:	963-132H

## Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 810 x 455 mm
Gross weight:	26,800 kg
Net weight:	22,300 kg
Shipping method:	Parcel service
UN number:	2800

## Construction

Casing material:	Cast aluminium alloys
Dimensions of display device (WxDxH):	300 x 190 x 230 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	5 kg
Precision (of [Max]):	0,200 %
Readability [d]:	500 g
Recommended adjusting weight:	5000 kg (M1)
Repeatability:	2,500 kg
Resolution:	10000
Stabilisation time under laboratory conditions:	2 s

# KERN HFM5T0.5



Robust industrial crane scale with bright LED display for optimum reading in unfavourable ambient conditions

Overall dimensions mounted 310 x 230 x 800 mm  
(WxDxH):

## Piktogramme

### STANDARD



### OPTION

