

KERN MBD20K-2S05

Ergonomically-optimised baby scale with large lying surface



Material weighing plate:	Plastic
Overall dimensions mounted (WxDxH):	597 x 350 x 74 mm
Weighing surface (WxD):	560 x 225 mm

Piktogramme

STANDARD



Measuring system

Linearity:	50 g
Readability [d]:	10 g
Repeatability:	10 g
Resolution:	1500
Tare range:	15 kg
Warm up time:	10 min
Weighing capacity [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	lb kg

Display

Display digit height (large):	3 cm
-------------------------------	------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

Power supply

Battery:	2x1.5 V AAA
Operating time:	20 h

Category

Brand:	KERN
Product Group:	Baby scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	480 x 654 x 177 mm
Gross weight:	30 kg
Net weight:	10 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	597 x 350 x 74 mm
Dimensions of weighing plate (WxDxH):	650 x 350 x 55 mm