

KERN PES6200-2M

Robust laboratory and industrial precision scale for heavy items, with EC type approval [M]



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	15 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH
Operating time (Backlight off):	32 h
Operating time (Backlight on):	6 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

DAkkS Certificate:	963-104
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	335 x 425 x 215 mm
Gross weight:	5,744 kg
Net weight:	4,336 kg
Shipping method:	Parcel service

Construction

Casing material:	Cast aluminium alloys
Dimensions housing (WxDxH):	220 x 333 x 93 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	220 x 333 x 93 mm
Weighing surface (WxD):	200 x 200 mm

Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
Minimum weight (USP):	20 g
Readability [d]:	10 mg
Recommended adjusting weight:	5 kg (E2)
Repeatability:	10 mg
Resolution:	620000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	4 h
Weighing capacity [Max]:	6,200 kg
Weighing units:	g ct kg

Display

Display digit height (large):	1,300 cm
-------------------------------	----------

Counting

Counting resolution:	620000
Minimum piece weight at piece counting (Laboratory):	10 mg
Minimum piece weight at piece counting (Normal):	100 mg

Functions

Capacity display:	yes
Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Weighing with tolerance range:	yes

KERN PES6200-2M



Robust laboratory and industrial precision scale for heavy items, with EC type approval [M]

Piktogramme

STANDARD



OPTION



FACTORY

