



NOTES

DESIGNED TO MEET THE REQUIREMENTS OF IP65, & NEMA 4X
 TONGUE & GROOVE CONSTRUCTION WITH A MOLDED ONE PIECE SILICON GASKET.
 COMES WITH 4 STAINLESS STEEL MACHINE LID SCREWS, CAPTIVATED WITH 4 RUBBER O-RINGS.
 COMES WITH 2 GROUNDING SCREWS AND WASHERS.
 FINISH: NONE OR SUFFIX "BK" BLACK, OR SUFFIX "GY" GRAY (RAL 7001) POLYESTER POWDER



SIDE VIEWS DO NOT DETAIL
 SCREW CHANNELS. SEE
 'A - A' FOR CHANNEL DETAIL



BOX

LID

For the best fit print
 on legal size paper.

THIS DRAWING IS PROPRIETARY INFORMATION OF
 HAMMOND MFG.CO.LTD. NOT TO BE USED WITHOUT
 EXPRESSED WRITTEN PERMISSION
 OF HAMMOND MFG.CO.LTD.

△	N/A	RELEASE	---	10/28/02	MJM
Rev	ECN	Description		Date	By

Unless otherwise spec'd dimensions are in millimeters Tolerances are:		Dwn	M. MERCER
X	±2.5	Date	10/28/02
.XX	±1.50	Chk	---
.XXX	±.500	Mat'l	CAST ALUMINUM
.XXXX	±.1300	Sheet	1 of 1
Holes	±.1300	Part #	1590Z135
Angles	±5°	Dwg:	1590Z135/A

HAMMOND MANUFACTURING CO. LTD. Electronics Group, Waterloo, Ont. - Cheektowaga, NY	
HAMMOND 1590Z SERIES CASTED AL ENCLOSURES	