

KRM55WR71H226MH01#


“#” indicates a package specification code.



< List of part numbers with package codes >

KRM55WR71H226MH01L KRM55WR71H226MH01K

Appearance & Shape



References

Packaging	Specifications	Minimum Order Quantity
L	180Embossed Tape	200
K	330Embossed Tape	500

Mass (typ.)	
1 piece	0.9g

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

KRM55WR71H226MH01#

“#” indicates a package specification code.

Specifications

Length	6.1±0.4mm
Width	5.3±0.2mm
Thickness	6.4±0.3mm
Capacitance	22μF ±20%
Metal terminal width e	1.2±0.2mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	50Vdc
Capacitance change rate	±15%
Temperature characteristics (complied standard)	X7R(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

KRM55WR71H226MH01#


"#" indicates a package specification code.

Characteristic Data


The charts below may show another part number which shares its characteristics.




■ KRM55WR71H226MH01 |Z| DCOV, 25degC



■ KRM55WR71H226MH01 R DCOV, 25degC



■ KRM55WR71H226MH01 C-DC bias capchange, 25.0degC, AC0.




■ KRM55WR71H226MH01 C-AC Voltage capchange, DCOV, 25.0d

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

KRM55WR71H226MH01#

“#” indicates a package specification code.



■ KRM55WR71H226MH01 C-Temp. capchange, DCOV, ACO, 5Vrms



KRM55WR71H226MH01 Temp. rise ■ 50kHz ■ 100kHz ■ 300kHz

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.