



## W62B, W62P & W62Y



CE Complex Design



### APPLICATIONS

Ideal for janitorial colour coding systems i.e. yellow in kitchens, pink in washrooms, etc.

### FEATURES AND BENEFITS

Flock lined, lightweight, natural latex glove

Range comprises three different colours: W62B – blue, W62P - pink, W62Y - yellow

Strong yet sensitive formulation

Tear resistant beaded cuff for easy donning

21 CFR (USA) compliant for food applications.

Size	Order code
<b>W62B</b>	
6.5 (S)	4744
7.5 (M)	4745
8.5 (L)	4746
9.5 (XL)	4747
<b>W62P</b>	
6.5 (S)	4760
7.5 (M)	4761
8.5 (L)	4762
9.5 (XL)	4763
<b>W62Y</b>	
6.5 (S)	4756
7.5 (M)	4757
8.5 (L)	4758
9.5 (XL)	4759
Length 300 mm	
Thickness (double wall) 0.85 mm	



## Soft Nitrile G21B



CE Complex Design



### APPLICATIONS

Ideal for use in printing, assembly work and food processing.

### FEATURES AND BENEFITS

Unique soft nitrile formulation with flock lining provides real comfort with protection

Superior raised grip pattern

All the protective properties of nitrile with the comfort of natural rubber

21 CFR (USA) and European Directives compliant for food applications.

Size	Order code
6.5 (S)	8047
7.5 (M)	8048
8.5 (L)	8049
9.5 (XL)	8050
10.5 (XXL)	8051
Length 345 mm	
Thickness (double wall) 0.70mm	



## Black Heavyweight™ G17K



CE Complex Design



### APPLICATIONS

Ideal for use in heavy industry, assembly, maintenance work and local authorities.

### FEATURES AND BENEFITS

Comfortable and sensitive natural rubber latex glove, yet withstands rough treatment

A tough general purpose industrial glove

High resistance to water based chemicals

Beaded cuff for tear resistance and easy pull on

Longer gauntlet style cuff for extra protection.

Size	Order code
6.5 (S)	1621
7.5 (M)	1622
8.5 (L)	1623
9.5 (XL)	1624
10.5 (XXL)	1625
Length 320 mm	
Thickness (double wall) 1.45mm	