MODEL MM7105-2D USB ThermoBarScan

Waterproof ThermoBarScan Thermometer with 1D/2D Scanner, Large Display & USB Connectivity

FEATURES

A handheld logging thermometer with integral barcode scanner for recording product location/identity plus time, date and temperature. This thermometer features a large display for more barcode information, scrolling buttons and USB connection to PC for data transmittal

- *** °C / °F switchable
- *** Resolution of 0.1° to 1000° autoranging
- *** Switchable thermocouple types K / T / J / R / N / E / S
- **** Infra-Red sensor compatability
- *** Full retention of thermocouple type and temperature scale
- *** User configurable Auto Swith Off capability
- *** Overrange / Open circuit sensor indication
- *** Low battery indication
- *** IP65 casing complete with protective rubber boot
- *** Integral Barcode reader for 1D and 2D barcode formats
- *** Supplied with USB connection cable
- *** Free downloadable software

SPECIFICATION

Environmental

AMBIENT OPERATING RANGE STORAGE TEMPERATURE RANGE HUMIDITY ELECTRICAL	:	0 to 50 °C -20 to 50 °C 0 to 70% R.H.
MEASUREMENT RANGES	:	K -200 to 1372 °C T -200 to 400 °C J -200 to 1200 °C R 0 to 1767 °C N -200 to 1200 °C E -200 to 1000 °C S 0 to 1767 °C
THERMOCOUPLE TYPES INFRA-RED SENSOR (Exergen K80) TEMPERATURE SCALES ACCURACY @23°C CHARACTERISING ACCURACY TEMPERATURE COEFFICIENT COLD JUNCTION COMPENSATION RESOLUTION		K T J R N E S K80 -50 to 250 °C °C / °F +/- 0.1% OF READING +/- 0.2 °C LESS THAN 0.05 °C 0.01% OF READING /°C 0.0075 °C/°C 0.1° to 1000, 1° ABOVE 1000
READABLE BARCODES		All UPC/EAN/JAN Codes EAN28 Codes Code39 Code128 PDF417 QR Code Data Matrix GS1-DataBarTM RSS, RSS Limited, RSS-14 RSS-14 Stacked, RSS-Expand

GENERAL BATTERY BATTERY LIFE (INTERMITTENT USE) WEIGHT DIMENSIONS

PP3 9V I.E.C. 6F22 GREATER THAN 200 HOURS (ALKALINE) 200 gms 160 X 50 X 30 mm

<u>Cross-reference for compatible probes</u> Suitable probes and accessories for use with this instrument

:

:

TME PART No	DESCRIPTION	APPLICATION	T/C TYPE
KP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	К
TP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
KP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	К
TP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
TP10	SOUS VIDE NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
KM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	К
TM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
KM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	К
TM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
KM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	К
TM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
KS01	SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	К
TS01-S	DUAL PROBE	FOR SURFACE AND IMMERSION MEASUREMENT	
KS07	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	К
TS04	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	Т
KS08	HIGH TEMP SURFACE PROBE	HIGH TEMPERATURE SURFACE MEASUREMENT	К
KA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	К
TA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	Т
TA12	SPATULA PROBE	BETWEEN PACK PROBE	Т
KH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	К
TH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	Т
KHA02	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	К
THA2	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	Т
KHM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	К
THM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
KHN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	К
THN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	Т
THA12	PLUG MOUNTED SPATULA PROBE	BETWEEN PACK PROBE	Т
KHS01	PLUG MOUNTED SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	К
KHS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	К
THS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	Т
PKHV1	HVAC KIT	PROBE KIT DESIGNED FOR THE HVAC INDUTRY	К
PKF1	FOOD KIT	PROBE KIT DESIGNED FOR THE FOOD INDUTRY	Т
PKGP1	GENERAL PURPOSE KIT	PROBE KIT CONTAINING MOST POPULAR PROBES	К
TP01	CORKSCREW PROBE	PROBE DESIGNED FOR CORE TEMPERATURE OF MEAT	Т
KPS10	PIPE CLAMP PROBE	PROBE DESIGNED TO BE CLAMPED ONTO PIPES	К
TFS01	FOOD SIMULANT PROBE	SIMULATES THE CORE TEMPERATURE OF FOOD IN HOT OR COLD STORAGE	

57-0120-04 V2