

# 1520 MegOhmMeter



Fluke 1520



## Insulation testing you can depend on

The Fluke 1520 MegOhmMeter is a handy insulation resistance tester that also measures voltage and checks connections with its Lo-Ohms function.

- Large, backlit LCD with analog bar graph and digital display
- Three output voltages for insulation resistance testing: 250V, 500V, 1000V
- Insulation resistance testing up to 4000 MΩ; switches automatically to voltage measurement when voltage is greater than 30V AC or 30V DC.
- ac/dc voltage measurement up to 600V

- Lo-Ohms function for testing connections
- Last reading memory display
- 4 C-cell batteries for up to 5,000 tests per EN61557-2, with battery-life indicator and auto shut-off.
- Autodischarge of capacitive voltage charges
- Rugged, splash-proof case with impact absorbing holster

## Specifications

Function	Range	Accuracy	Resolution
<b>Insulation Resistance</b>			
Auto ranges	4.000 MΩ, 40.00 MΩ, 400.0 MΩ, 4000 MΩ	To 100 MΩ: 2% + 2 counts over 100 MΩ: 10% + 2 counts + 1%/GΩ	0.001 MΩ to 10 MΩ
Test voltages	250V, 500V, 1000V	+ 20%, - 0%	
Max. measurement current	1 mA		
Audible/visible voltage warning	≥30V ac or dc		
<b>Lo-Ohms</b>			
Resistance	0 to 40.00Ω	2% + 2 counts	0.01Ω
Analog bar graph	0 to 100Ω		
Audible/visible voltage warning	≥30V ac or dc		
<b>Resistance</b>			
Resistance	4 kΩ	2% + 2 counts	1Ω
Analog bar graph	0 to 10kΩ		
<b>Voltage</b>			
Voltage	0 to 600V ac (50/60 Hz)	2% + 2 counts	1V

**Operating Temperature:** -10°C to +50°C

**Storage Temperature:** -40°C to +70°C

**Humidity (Without Condensation):**

75% RH (40°C)

**Dust/ water resistance:** IP42 per IEC 529

**Operating Altitude:** 2,500 meters

**Batteries:** 4 C size 1.5V alkaline

**Size (HxWxD):** 241 mm x 108 mm x 72 mm

**Weight:** 1.1 kg

**Three Year Warranty**

### Included Accessories

TL27 heavy duty test leads, TP74 lantern tip test probes, AC285 large jaw alligator clips, protective holster with hand strap, C43 carrying case, instruction manual

### Ordering Information

Fluke 1520 MegOhmMeter

### Recommended Accessories



SH100



TL223



TPAK



L210



TL27