



SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/8

Pro-Power Screen Wash -15

Revision 1
Revision date 2016-08-30

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	Pro-Power Screen Wash -15
--------------	---------------------------

1.2. Relevant identified uses of the substance or mixture and uses advised against

Product Use	[SU21] Consumer uses: Private households (= general public = consumers); ----- [SU22] Professional uses: Public domain (administration, education, entertainment, services, craftsmen);
Description	Screen Wash.

1.3. Details of the supplier of the safety data sheet

Company	Future Developments Manufacturing Ltd
Address	Davenport Street Burslem Stoke on Trent ST6 4HS Staffordshire
Web	www.fdev.co.uk
Telephone	01782 826870
Fax	01782 816392
Email	sales@fdev.co.uk
Email address of the competent person	support@fdhost.co.uk

1.4. Emergency telephone number

Emergency telephone number	01782 829000 9.00am-5.00pm Mon - Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.1. Classification - 1999/45/EC	T; R23/24/25-39/23/24/25 R10 Symbols: T: Toxic.
Main hazards	Flammable. Toxic by inhalation, in contact with skin and if swallowed. Toxic: danger of very serious irreversible effects through inhalation, in contact with skin and if swallowed.
2.1.2. Classification - EC 1272/2008	Flam. Liq. 3: H226; Acute Tox. 4: H302; Acute Tox. 4: H312; Acute Tox. 4: H332; STOT SE 1: H370;

2.2. Label elements

Hazard pictograms	
Signal Word	Danger

Pro-Power Screen Wash -15

Revision 1
Revision date 2016-08-30

2.2. Label elements

Hazard Statement	Flam. Liq. 3: H226 - Flammable liquid and vapour. Acute Tox. 4: H302 - Harmful if swallowed. Acute Tox. 4: H312 - Harmful in contact with skin. Acute Tox. 4: H332 - Harmful if inhaled. STOT SE 1: H370 - Causes damage to organs .
Precautionary Statement: Prevention	P102 - Keep out of reach of children P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P233 - Keep container tightly closed. P240 - Ground/bond container and receiving equipment. P241 - Use explosion-proof electrical/ventilating/lighting// equipment. P242 - Use only non-sparking tools. P243 - Take precautionary measures against static discharge. P260 - Do not breathe dust/fume/gas/mist/vapours/spray. P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P264 - Wash thoroughly after handling. P270 - Do not eat, drink or smoke when using this product. P271 - Use only outdoors or in a well-ventilated area. P280 - Wear protective gloves/protective clothing/eye protection/face protection.
Precautionary Statement: Response	P301+P312 - IF SWALLOWED: Call a POISON CENTER/doctor/ /if you feel unwell. P302+P352 - IF ON SKIN: Wash with plenty of water/ . P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing. P312 - Call a POISON CENTER/doctor/ /if you feel unwell. P321 - Specific treatment (see on this label). P330 - Rinse mouth. P370+P378 - In case of fire: Use to extinguish.
Precautionary Statement: Storage	P403+P235 - Store in a well-ventilated place. Keep cool. P405 - Store locked up.
Precautionary Statement: Disposal	P501 - Dispose of contents/container to local and national regulations

2.3. Other hazards

Other hazards	No further relevant information available.
---------------	--

SECTION 3: Composition/information on ingredients

3.2. Mixtures

67/548/EEC / 1999/45/EC

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification	M-factor.
Methanol	603-001-00-X	67-56-1	200-659-6		20 - 30%	F; R11 T; R23/24/25-39/23/24/25	

Pro-Power Screen Wash -15

Revision 1

Revision date 2016-08-30

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification	M-factor.
Benzenesulfonic acid, 4-C10-13-sec-alkyl derivs.,compds.with triethanolamine		121617-08-1	939-464-2		0 - 0.5%	Skin Irrit. 2: H315; Eye Dam. 1: H318;	
Amides, C8-18(even-numbered) and C18 (unsatd.), N,N-bis(hydroxyethyl) Methanol	603-001-00-X	67-56-1	200-659-6	931-329-6	0 - 0.5%	Skin Irrit. 2: H315; Eye Dam. 1: H318; Aquatic Chronic 2: H411;	
Protectol BN		52-51-7	200-143-0		20 - 30%	Flam. Liq. 2: H225; Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT SE 1: H370;	
					0 - 0.5%	Acute Tox. 4: H302; Acute Tox. 4: H312; Skin Irrit. 2: H315; STOT SE 3: H335;	M=10

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Harmful by inhalation. Inhalation may cause nausea and vomiting. Move the exposed person to fresh air. If you feel unwell, seek medical advice (show the label where possible).
Eye contact	May cause irritation to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	Harmful in contact with skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
Ingestion	Harmful if swallowed. Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist. DO NOT INDUCE VOMITING.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	See section 4.1 for further information.
Eye contact	See section 4.1 for further information.
Skin contact	See section 4.1 for further information.
Ingestion	See section 4.1 for further information.

4.3. Indication of any immediate medical attention and special treatment needed

	No further relevant information available.
--	--

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Use extinguishing media appropriate to the surrounding fire conditions.
--	---

5.2. Special hazards arising from the substance or mixture

	Burning produces irritating, toxic and obnoxious fumes.
--	---

5.3. Advice for firefighters

	Wear suitable respiratory equipment when necessary.
--	---

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

	Ensure adequate ventilation of the working area. Wear suitable protective equipment.
--	--

6.2. Environmental precautions

	Do not allow product to enter drains. Prevent further spillage if safe.
--	---

6.3. Methods and material for containment and cleaning up

	Absorb with inert, absorbent material. Sweep up. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.
--	---

Pro-Power Screen Wash -15

Revision 1

Revision date 2016-08-30

6.4. Reference to other sections

See section 2,3,8,13 for further information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Adopt best Manual Handling considerations when handling, carrying and dispensing.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated area. Keep containers tightly closed. Store in correctly labelled containers.

7.3. Specific end use(s)

See section 1.2 for further information.

SECTION 8: Exposure controls/personal protection


8.1. Control parameters

See section 8.2 for further information.

8.1.1. Exposure Limit Values

Methanol	WEL 8-hr limit ppm: 200	WEL 8-hr limit mg/m3: 266
	WEL 15 min limit ppm: 250	WEL 15 min limit mg/m3: 333
	WEL 8-hr limit mg/m3 total - inhalable dust:	WEL 15 min limit mg/m3 total - inhalable dust:
	WEL 8-hr limit mg/m3 total - respirable dust:	WEL 15 min limit mg/m3 total - respirable dust:

8.2. Exposure controls



8.2.1. Appropriate engineering controls

Ensure adequate ventilation of the working area.

8.2.2. Individual protection measures

Wear chemical protective clothing.

Eye / face protection

Approved safety goggles.

Skin protection -
Handprotection

Chemical resistant gloves (PVC).

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Pro-Power Screen Wash -15

Revision 1
Revision date 2016-08-30

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Various
Odour	Characteristic
pH	7 - 8
Melting point	Not applicable.
Freezing Point	-20 °C
Initial boiling point	Not applicable.
Flash point	38 °C
Evaporation rate	No data available
Flammability (solid, gas)	Not applicable.
Relative density	No data available
Fat Solubility	No data available
Partition coefficient	No data available
Autoignition temperature	Not applicable.
Viscosity	No data available
Explosive properties	Not applicable.
Oxidising properties	Not applicable.
Solubility	Soluble in water

9.2. Other information

Conductivity	No data available
Surface tension	No data available

SECTION 10: Stability and reactivity

10.1. Reactivity

	Stable under normal conditions.
--	---------------------------------

10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

10.3. Possibility of hazardous reactions

	No data is available on this product.
--	---------------------------------------

10.4. Conditions to avoid

	No data is available on this product.
--	---------------------------------------

10.5. Incompatible materials

	No data available.
--	--------------------

10.6. Hazardous decomposition products

	No data is available on this product.
--	---------------------------------------

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	Harmful if swallowed.
Skin corrosion/irritation	Harmful in contact with skin.
Respiratory or skin sensitisation	May be harmful if inhaled.
Germ cell mutagenicity	No data is available on this product.
Carcinogenicity	No data is available on this product.
Reproductive toxicity	No data is available on this product.

11.1.4. Toxicological Information

Pro-Power Screen Wash -15

Revision 1
Revision date 2016-08-30

11.1.4. Toxicological Information

No data available

SECTION 12: Ecological information

12.1. Toxicity

No data available

12.2. Persistence and degradability

No data is available on this product.

12.3. Bioaccumulative potential

No data is available on this product.

Partition coefficient

Michelin Screen Wash -20 No data available

12.4. Mobility in soil

No data is available on this product.

12.5. Results of PBT and vPvB assessment

No data is available on this product.

12.6. Other adverse effects

However, large or frequent spills may have hazardous effects on the environment. The product is not regarded as dangerous for the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Must be disposed of in accordance with local and national regulations.

General information

Dispose of in compliance with all local and national regulations.

SECTION 14: Transport information

Hazard pictograms



14.1. UN number

UN1993

14.2. UN proper shipping name

FLAMMABLE LIQUID, N.O.S.

14.3. Transport hazard class(es)

ADR/RID	3
Subsidiary risk	-
IMDG	3
Subsidiary risk	-
IATA	3
Subsidiary risk	-

Pro-Power Screen Wash -15

Revision 1

Revision date 2016-08-30

14.4. Packing group	
Packing group	III
14.5. Environmental hazards	
Environmental hazards	No
Marine pollutant	No
ADR/RID	
Hazard ID	30
Tunnel Category	(D/E)
IMDG	
EmS Code	F-E S-E
IATA	
Packing Instruction (Cargo)	366
Maximum quantity	220 L
Packing Instruction (Passenger)	355
Maximum quantity	60 L
Further information	
	The product is not classified as dangerous for carriage.
SECTION 15: Regulatory information	
15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture	
	The classification detailed on this safety data sheet refers to the neat material only. Dilution of the product may reduce the classification. This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006 & (EC) No. 1272/2008 & (EC) 1999/45.
15.2. Chemical safety assessment	
	No information available.
SECTION 16: Other information	
Other information	
Revision	This document differs from the previous version in the following areas:. 2 - 2.1. Classification of the substance or mixture. 2 - 2.1.2. Classification - EC 1272/2008. 2 - Hazard pictograms. 2 - Signal Word. 2 - Precautionary Statement: Prevention. 2 - Precautionary Statement: Response. 2 - Precautionary Statement: Storage. 4 - Skin contact. 4 - Inhalation. 4 - Ingestion. 8 - 8.2.1. Appropriate engineering controls. 9 - 9.1. Information on basic physical and chemical properties (Colour). 9 - 9.1. Information on basic physical and chemical properties (Flash point). 11 - Acute toxicity. 11 - Skin corrosion/irritation. 11 - Respiratory or skin sensitisation. 11 - Serious eye damage/irritation. 12 - 12.1. Toxicity. 12 - 12.6. Other adverse effects. 15 - Labelling. 15 - Risk phrases.

Pro-Power Screen Wash -15

Revision 1

Revision date 2016-08-30

Other information

Text of risk phrases in Section 3	<p>15 - Safety phrases.</p> <p>R11 - Highly flammable. R23/24/25 - Toxic by inhalation, in contact with skin and if swallowed. R39/23/24/25 - Toxic: danger of very serious irreversible effects through inhalation, in contact with skin and if swallowed.</p>
Text of Hazard Statements in Section 3	<p>Skin Irrit. 2: H315 - Causes skin irritation. Eye Dam. 1: H318 - Causes serious eye damage. Aquatic Chronic 2: H411 - Toxic to aquatic life with long lasting effects. Flam. Liq. 2: H225 - Highly flammable liquid and vapour. Acute Tox. 3: H301 - Toxic if swallowed. Acute Tox. 3: H311 - Toxic in contact with skin. Acute Tox. 3: H331 - Toxic if inhaled. STOT SE 1: H370 - Causes damage to organs . STOT SE 2: H371 - May cause damage to organs . Acute Tox. 4: H302+H312 - Harmful if swallowed or in contact with skin STOT SE 3: H335 - May cause respiratory irritation.</p>

Further information

	<p>The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.</p>
--	---