


NAIS**POLARISED, MONOSTABLE
RELAY WITH FORCIBLY
GUIDED CONTACTS****SF2-RELAY**

Tolerance ± 0.3
Weight approx 37 g

- Relay complying with EN 50 205, Type A
- TÜV / UL / CSA / SEV
- Overvoltage category as per IEC 60664-1 III/4kV

- Rated voltage in [V] as per IEC 60664-1, basic insulation

	Pollution degree		
	2 inside	2 outside	3 outside
Coil-Contact	400	400	250
Contact-Contact	400	400	400

Characteristics

Contact configuration (a = normally open, b = normally closed)	2a 2b
Contact material	AgSnO ₂ with Au flash
Volume resistance (initial at 6 V DC, 1A)	m 30
Making and breaking capacities according EN 60947-5-1: 1997, table 4 AC15/DC13 ¹⁾	6A 250 V / 3A 24V
Max. switching voltage	V 400
Min. switching voltage / min. switching current	V/mA 10/10
Pick-up / nominal power consumption at 20°C	mW 280/500
Pick-up/drop-out voltage in % of nominal voltage at 20°C	% 75/10
Pick-up/drop-out/bounce time (approx. values at U _{rated})	ms 16/7/2
Max. switching frequency (without load)	Hz 10
Mechanical operation life (electrical life see below)	ops 10 ⁷
Permissible ambient temperature at rated power consumption	°C -40 / +70
Upper temperature limit	°C 105
Test voltage open contact / contact-contact / contact-coil	V _{rms} 2500 / 2500 / 2500
Insulation resistance at 500 V DC (initial)	10 ⁹
Shock resistance (11 ms) ²⁾	g 30
Vibration resistance 10 – 200 Hz (10 – 55 Hz, amplitude 2 mm) ²⁾	g 10
Solder bath temperature (max. duration)	°C/s 260 / 5
Degree of protection	IP67 / IP30 ¹⁾

1) Breathing hole open 2) Contact interruption <10µs

Ordering information / Coil data



Partnumber	Coil nominal voltage (V)	Pick-up voltage (V)	Drop-out voltage (V)	Coil resistance () $\pm 10\%$, 20°C	Coil inductance (mH)
SF2-5V	5	3.75	0.5	50	47
SF2-9V	9	6.75	0.9	162	145
SF2-12V	12	9	1.2	288	252
SF2-18V	18	13.5	1.8	648	551
SF2-21V	21	15.75	2.1	882	742
SF2-24V	24	18	2.4	1152	959
SF2-36V	36	27	3.6	2592	2097
SF2-48V	48	36	4.8	4608	3654
SF2-60V	60	45	6	7200	5612

Electrical life

Voltage	Current	Load type	Frequency	Duty cycle	No. of contacts	No. of ops.
250 V AC	8 A	cos $\varphi = 1$	0.33 Hz	50%	4 ⁴⁾	30 000 ³⁾
250 V AC	6 A	cos $\varphi = 1$	0.33 Hz	50%	4 ⁴⁾	100 000 ³⁾
250 V AC	2 A	cos $\varphi = 1$	0.33 Hz	50%	4 ⁴⁾	500 000 ³⁾
220 V AC	30/3 A	AC15 ⁵⁾	0.10 Hz	10%	1 ⁵⁾	200 000 ³⁾
220 V AC	5.10 A	cos $\varphi = 0.60$	0.20 Hz	10%	1 ⁵⁾	100 000 ³⁾
220 V AC	4.43 A	cos $\varphi = 0.35$	0.20 Hz	50%	1 ⁵⁾	100 000 ³⁾
220 V AC	1.45 A	cos $\varphi = 0.35$	0.20 Hz	50%	1 ⁵⁾	300 000 ³⁾
24 V DC	6 A	resistive	0.33 Hz	50%	4 ⁴⁾	400 000 ³⁾
24 V DC	2 A	resistive	0.50 Hz	50%	4 ⁴⁾	2 Mio. ³⁾
24 V DC	3 A	DC13 ⁵⁾	0.33 Hz	10%	1 ⁵⁾	50 000 ³⁾
24 V DC	3 A	L/R = 40 ms	0.33 Hz	10%	1 ⁵⁾	100 000 ³⁾

3) Ambient temperature +70°C 4) Breathing hole closed 5) Breathing hole open 6) EN 60947-5-1: 1997; table C.1

Note: Suitable for most common washing methods except ultrasonic cleaning.


**Application notes**

If required a breathing hole can be made in the cover by removing the nipple. However be aware that the degree of protection will reduce from IP67 to IP30!

Relay characteristics are influenced by


- strong external magnetic fields
- magnetic conductive materials near the relay
- narrow top-to-top mounting (printed surface to printed surface)

Load limit curve




Loads in the range under the curve can be switched safely. The arc will extinguish before the opposite contact makes.

Coil voltage characteristics




Permissible coil voltages and pick-up and drop-out characteristics at various ambient temperatures.

Connection diagram and pcb bore hole data




The contacts are shown in the deenergized condition.



Grid 2.54

Contact current characteristics



--- U coil = 0% Load on NC 5-6
 — U coil = 100% Load on all NO
 The curves are determined by the contact resistance