


RoHS
Compliant



Description

Solid 23AWG PACW, UTP 4Pairs, PE Insulation, Cross-web Separator, Water Resistant Flooding Compound, PE Sheath.

Application

The cable is suitable for outdoor use in duct and for aerial lashing. It is water blocked and has a black sunlight resistant. For high speed data transmission.

IEEE802.3 10BASE-T (ETHERNET)
IEEE802.3 100BASE-T (Fast ETHERNET)
IEEE802.3 1000BASE-T (Gigabit ETHERNET)
IEEE802.5 4/16 Mbps Token Ring
52/155Mbps ATM
100VG-AnyLAN
ANSI X3T9.5 100Mbps TP-PMD

Applicable Standard

ANSI/TIA-568-C.2
IEC 60794-1-2-F5B

Construction

Conductor

Material : Plain Annealed Copper Wire
Size : 23AWG
Construction : Solid

Insulation

Material : PE
Nominal O.D : 1.015mm
Colour : Blue/White-Blue Stripe, Orange/White-Orange Stripe,
Green/White-Green Stripe, Brown/White-Brown Stripe

Filler

Material : Cross-web Separator
Water Resistant Flooding Compound

Sheath

Material : PE
Nominal O.D : 7.3mm
Colour : Black

Physical Properties

Min. Bend Radius : 73mm
Operating Temperature : -30°C to +70°C

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

Electrical Properties


Max. Operating Voltage (UL) : 300V
 Max. DC Resistance @20°C : 73.16Ω/km
 Max. DCR Unbalance @20°C : 5%
 Voltage test : Core to Core : 1.5 kV AC/1min
 Nom. Mutual Capacitance @ 1kHz : 56pF/m

Transmission Performance

Nom. Velocity of Propagation : 64%
 Max. Propagation Delay Skew : 45 ns/100m
 Max. Capacitance Unbalance @ 20°C : 330pF/100m
 Characteristic Impedance (1-250MHz) : 100 ±15Ω

Freq. (MHz)	Max. IL (dB/100m)	Min. NEXT (dB/100m)	Min. PSNEXT (dB/100m)	Min. RL (dB/100m)	Min. ELFEXT (dB/100m)	Min. PSELFEXT (dB/100m)	Min. LCL (dB/100m)	Min. TCL (dB/100m)	Min. ELTCTL (dB/100m)
1	2.03	74.3	72.3	20	67.8	64.8	40	40	35
4	3.78	65.27	63.27	23.01	55.76	52.76	40	40	23
8	5.32	60.75	58.75	24.52	49.74	46.74	40	40	16.9
10	5.95	59.3	57.3	25	47.8	44.8	40	40	15
16	7.55	56.24	54.24	25	43.72	40.72	38	38	10.9
20	8.47	54.78	52.78	25	41.78	38.73	37	37	9
25	9.5	53.33	51.33	24.32	39.84	36.84	36	36	7
31.25	10.67	51.88	49.88	23.64	37.9	34.9	35.1	35.1	5.5
62.5	15.38	47.36	45.36	21.54	31.88	62.5	32	32	*
100	19.8	44.3	42.3	20.11	27.8	24.8	30	30	*
155	-	-	-	21	-	-	-	-	*
200	28.98	39.78	37.78	18	21.78	18.78	27	27	*
250	32.85	38.33	36.33	17.32	19.84	16.84	26	26	*

Diagram



Part Number Table

Description	Part Number
Cable, Outdoor CAT 6, Black, 305m	PP001510

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.