

# H05RR-F / 318-TRS

## Tough Rubber Cable

**multicomp** PRO

**RoHS  
Compliant**



### Application:

Flexible cords suitable for use in domestic premises, such as kitchens and offices.

### Construction:

#### Conductor:

Class 5 flexible copper conductor according to BS EN 60228 (previously BS 6360)

#### Insulation:

Rubber compound type E14 according to BS EN 50363

#### Sheath:

Rubber compound type EM3 according to BS EN 50363

### Cable Standards

Made in accordance with the following:  
BS EN 50525-2-21, VDE0282 (BS 6500)

### Characteristics:

#### Voltage Rating (Uo/U)

300/500V

#### Temperature Rating:

Flexed : -25°C to +60°C

#### Min. Bending Radius:

Flexed : 4 × overall diameter

Fixed : 3 × overall diameter

#### Core Identification:

2 core : Brown and Blue

3 core : Green/Yellow, Blue and Brown

4 core : Green/Yellow, Brown, Black and Grey

#### Sheath Colour:

Black

[Newark.com/multicomp-pro](http://Newark.com/multicomp-pro)  
[Farnell.com/multicomp-pro](http://Farnell.com/multicomp-pro)  
[Element14.com/multicomp-pro](http://Element14.com/multicomp-pro)

**multicomp** PRO

# H05RR-F / 318-TRS

## Tough Rubber Cable

**multicomp** PRO

### Dimensions:

Part Number	No. of Cores	Nominal Cross Sectional Area mm <sup>2</sup>	Nominal Thickness of Insulation mm	Nominal Overall Diameter mm	Nominal Weight kg/km
PP001147	2	1	0.6	6.6	64
PP001150		1.5	0.8	7.8	95
PP002186	3	0.75	0.6	6.6	65
PP001148		1	0.6	7	77
PP001151		1.5	0.8	8.4	115
PP001153	4	2.5	0.9	9.9	170
PP001149		1	0.6	7.6	95
PP001152		1.5	0.8	9.4	145

### Conductors

Class 5 Flexible Copper Conductors for Multi-Core Cables

Nominal Cross Sectional Area mm <sup>2</sup>	Max. Diameter of Wires in Conductor mm	Max. Resistance of Conductor at 20°C Plain Wires $\Omega / km$
0.75	0.21	26
1	0.21	19.5
1.5	0.26	13.3
2.5	0.26	7.98

The above table is in accordance with BS EN 60228 (previously BS 6360)

### Electrical Characteristics:

Current Carrying Capacity and Mass Supportable

Nominal Cross Sectional Area mm <sup>2</sup>	Current Carrying Capacity Amps		Max. Mass Supportable by Twin Flexible Cord (See Regulations 522.7.2 and 559.6.1.5 from 17th Edition of Wiring Regulations) kg
	Single-Phase AC	Three-Phase AC	
0.75	6	6	3
1	10	10	5
1.5	16	16	
2.5	25	20	

The above table is in accordance with Table 4F3A of the 17th Edition of IEE Wiring Regulations.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO

# H05RR-F / 318-TRS Tough Rubber Cable



## Voltage Drop:

Nominal Cross Sectional Area mm <sup>2</sup>	DC or Single-Phase AC mV/A/m	Three-Phase AC mV/A/m
0.75	62	54
1	46	40
1.5	32	27
2.5	19	16

Conductor operating temperature: 60°C

The above table is in accordance with Table 4F3B of the 17th Edition of IEE Wiring Regulations.

## De-Rating Factors:

De-Rating Factor for Ambient Temperature 60°C Thermoplastic or Thermosetting Insulated Cords

Ambient Temperature	35°C	40°C	45°C	50°C	55°C
De-Rating Factor	0.91	0.82	0.71	0.58	0.41

## Part Number Table

Description	Reel Length	Part Number
H05RR-F / 318-TRS Tough Rubber Cable, 2 Core, 1mm <sup>2</sup> , Black	50m or per metre	PP001147
H05RR-F / 318-TRS Tough Rubber Cable, 2 Core, 1.5mm <sup>2</sup> , Black		PP001150
H05RR-F / 318-TRS Tough Rubber Cable, 3 Core, 0.75mm <sup>2</sup> , Black		PP002186
H05RR-F / 318-TRS Tough Rubber Cable, 3 Core, 1mm <sup>2</sup> , Black		PP001148
H05RR-F / 318-TRS Tough Rubber Cable, 3 Core, 1.5mm <sup>2</sup> , Black		PP001151
H05RR-F / 318-TRS Tough Rubber Cable, 3 Core, 2.5mm <sup>2</sup> , Black		PP001153
H05RR-F / 318-TRS Tough Rubber Cable, 4 Core, 1mm <sup>2</sup> , Black		PP001149
H05RR-F / 318-TRS Tough Rubber Cable, 4 Core, 1.5mm <sup>2</sup> , Black		PP001152

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

