


Aluminium Standard – 01.23 40 23

Aluminium enclosure consisting of lid, seal, incl. captive +/-stainless steel screws, base with 2 or 4 earthing screws



Dimensions H x W x D (mm)	230 x 400 x 225
Weight (g)	7970
Order number	01.23 40 23
Product type	ALS 01190

- + Robust aluminium enclosure for mechanical engineering and automation technology
- + Fixing options for DIN rails and mounting plates
- + Usable in wide temperature area




Technical Data

Material	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Powder coating, RAL 7001, silver grey, special colour on request
Ingress protection	IP 66 to EN 60529, higher protection on request
Impact resistance	7 Joule in reference to EN 60079-0
Temperature range	PU (polyurethane) seal (std.): -40°C to +90°C CR (chloroprene) seal: -40°C to +100°C VMQ (silicone) seal (optional): -60°C to +130°C
Other versions on request	EMC, SBG, SBGL, SWB, Silicone lid seal

Aluminium Standard – 01.23 40 23

Number of cable glands

Maximum number of cable glands to DIN 50262*



M	PG	Side	
		A/B	C/D
12	17,25	240	108
16	25,30	122	48
20	27,60	100	44
25	37,95	54	21
32	48,30	30	13
40	60,95	18	9
50	69,00	15	6
63	74,75	12	5
75			
85			

Commercial Data

Country of origin	HU
Pieces per packaging	1
Customs tariff number	76169990
Weight (g)	7970
GTIN	4250157900364

ETIM Classification

ETIM-Class	EC000058
------------	----------

Accessories

Description	Order number
External mounting brackets set = 4 pcs	10.03 11 02
External hinges Swivelling range 150°set = 2 pcs	10.02 70 01
Internal hinges swivelling range 95°, set = 2 pcs	10.02 20 01
Turn bolt fastener	12.01 62 01
DIN rails TS 35/7,5	10.06 14 27
Earth rail	10.06 20 11
Mounting plate	10.01 10 18
Allen lid screws	12.01 80 04